

Flat suction cup (round)

PFG 150 NBR-55 N010

Osanro.:10.01.01.00333

<https://www.schmalz.com/10.01.01.00333>

Aloitussivu > Alipainetekniikkaa automaatioon > Alipaineekomponentit > Imukupit > Litteä imukuppi (pyöreä) > PFG 150 NBR-55 N010

Flat suction cup (round) for smooth or slightly rough surfaces




Size: 150

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Suunnitteludata



Attribuutti	Arvo
d	7 mm
Dk	104,50 mm
Dmax(S)	158 mm
Ds	147,50 mm
H	31 mm
Z (Stroke)	9 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Tekniset tiedot

Attribuutti	Arvo
Suction force (-600mbar)	842 N
Volume	164,71 cm ³
Curve radius (min) (convex)	300 mm
Size	150
Nipple family	N 010
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55 Shore A
Weight	411,30 g

Ota yhteyttä Schmalziin

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Flat suction cup (round)

PFG 150 NBR-55 N010

Osanro.:10.01.01.00333

<https://www.schmalz.com/10.01.01.00333>

Product family

PFG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Lisätarvikkeet



SA-NIP N010 G1/2-IG

Osanro.:10.01.01.00796

Thread G1: G1/2"-F

Material: Aluminum



SU 160

Osanro.:10.01.01.12438

Size: 160

Clamping range: 150.0 ... 180.0 mm

Temperature resistance: 80 °C