

## Robots-Set FXCB

ROB-SET FXCB UR SPB2

Osanro.:10.01.43.00128

<https://www.schmalz.com/10.01.43.00128>

Aloitussivu > Alipainetekniikkaa automaatioon > Alipaineekomponentit > Alueen tartuntajärjestelmät ja päätehosteet > Alueen tartuntajärjestelmät FXCB / FMCB > Handling Sets FXCB > ROB-SET FXCB UR SPB2

### Complete vacuum system for connecting to lightweight robots




for: Universal Robots

Type: 3,5,10,16

Construction shape vacuum switch: NPN switching

Control valve: Normally open

### Suunnitteludata



| Attribuutti | Arvo      |
|-------------|-----------|
| B           | 123,20 mm |
| B1          | 159 mm    |
| H           | 158 mm    |
| H1          | 164 mm    |
| H2          | 47 mm     |
| L           | 297 mm    |
| L1          | 331 mm    |
| L2          | 114,40 mm |
| L3          | 102 mm    |
| dn          | 10 mm     |

### Tekniset tiedot

| Attribuutti              | Arvo             |
|--------------------------|------------------|
| Weight                   | 2,20 kg          |
| Suction rate (max.)      | 525,90 l/min     |
| Number of suction cells  | 15               |
| Lift capacity (vertical) | 80 N             |
| Max. load (horizontal)   | 350 N            |
| for                      | Universal Robots |
| Product family           | ROB-SET-FXCB     |

### Ota yhteyttä Schmalziin

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | [schmalz@schmalz.fi](mailto:schmalz@schmalz.fi)

## Robots-Set FXCB

ROB-SET FXCB UR SPB2

Osanro.:10.01.43.00128

<https://www.schmalz.com/10.01.43.00128>

The technical properties of the robot types may vary by region. The stated compatibility of the set is based on standard European models.

### Varaosat



#### EMVP 2.35 24V-DC 2x3/2 NO/NC CAR

Osanro.:10.01.11.03420

Length L: 82,1 mm

Width B: 53,7 mm

Height H: 10,8 mm



#### SD 97x34x20 FXCB

Osanro.:10.01.43.00005

Length L: 97 mm

Width B: 34 mm

Height H: 20 mm



#### VSi V D M8-4

Osanro.:10.06.02.00577

Measuring range: -1,0 ... 0,0 bar

Construction shape vacuum switch: with display

Electrical connection: Male connect M8, 4 pole

Indication: 2xLED

Protection type IP: IP 65

## Robots-Set FXCB

ROB-SET FXCB UR SPB2

Osanro.:10.01.43.00128

<https://www.schmalz.com/10.01.43.00128>



### SPB2 40 SI-55 P

Osanro.:10.01.06.03126

Size: 40

Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Number of folds: 2,5

Shape: Push In