

Robots-Set FXCB

ROB-SET FXCB FANUC O20

Osanro.:10.01.43.00149

<https://www.schmalz.com/10.01.43.00149>

Aloitussivu > Alipainetekniikkaa automaatioon > Alipaineekomponentit > Alueen tartuntajärjestelmät ja päätehosteet > Alueen tartuntajärjestelmät FXCB / FMCB > Handling Sets FXCB > ROB-SET FXCB FANUC O20

Complete vacuum system for connecting to lightweight robots




for: FANUC

Type: CRX

Construction shape vacuum switch: NPN switching

Control valve: Normally open

Suunnitteludata



Attribuutti	Arvo
B	130 mm
B1	159 mm
H	131,40 mm
H1	137,40 mm
H2	20 mm
L	300 mm
L1	331 mm
L2	99 mm
L3	102 mm
dn	10 mm

Tekniset tiedot

Attribuutti	Arvo
Weight	2 kg
Suction rate (max.)	525,90 l/min
Material type	Foam O, Height 20 mm
Number of suction cells	45
Lift capacity (vertical)	80 N
Max. load (horizontal)	350 N
for	FANUC
Product family	ROB-SET-FXCB

Ota yhteyttä Schmalziin

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Robots-Set FXCB

ROB-SET FXCB FANUC O20

Osanro.:10.01.43.00149

<https://www.schmalz.com/10.01.43.00149>

The technical properties of the robot types may vary by region. The stated compatibility of the set is based on standard European models.

Varaosat



EMVP 2.35 24V-DC 2x3/2 NO/NC CAR

Osanro.:10.01.11.03420

Length L: 82,1 mm

Width B: 53,7 mm

Height H: 10,8 mm



SD 97x34x20 FXCB

Osanro.:10.01.43.00005

Length L: 97 mm

Width B: 34 mm

Height H: 20 mm



VSi V D M8-4

Osanro.:10.06.02.00577

Measuring range: -1,0 ... 0,0 bar

Construction shape vacuum switch: with display

Electrical connection: Male connect M8, 4 pole

Indication: 2xLED

Protection type IP: IP 65

Robots-Set FXCB

ROB-SET FXCB FANUC O20

Osanro.:10.01.43.00149

<https://www.schmalz.com/10.01.43.00149>



DI-PL 300x130 3R18 LL-20x7 O20 KE

Osanro.:10.01.11.03658

Length L: 300 mm

Width B: 130 mm

Height H: 20 mm

Construction use: Vacuum area gripping system

Arrangement: 3R18

Add. function: Adhesive tape on one side