

Robots-Set ECBPMi

ROB-SET PLUS ECBPMi UR

Osanro.:10.03.01.00617

<https://www.schmalz.com/10.03.01.00617>

Aloitussivu > Alipainetekniikkaa automaatioon > Alipaineekomponentit > Tyhjiögeneraattori > Alipaineentuotto End-of-Arm > Handling Sets ECBPMi > ROB-SET PLUS ECBPMi UR

Complete set for connecting and integrating the CobotPump ECBPMi to lightweight robots



Add. function: PLUS

for: Universal Robots


Type: UR3/5

contains: Suction cup

and: Screws

Degree of evacuation: 60 %

Suunnitteludata



Attribuutti	Arvo
Lk	120,50 mm
D	63 mm
D2	31,50 mm
D mk1	46 mm
D mk2	50 mm
G1	M4-F
G2	G1/4"-F
G4	M8-F
L	67,40 mm
L1	73,40 mm
LG1	6 mm
LG2	11,50 mm

Tekniset tiedot

Attribuutti	Arvo
Suction rate (max.)	1,60 l/min
Degree of evacuation	60 %
Voltage DC	24V - DC
Rated power	7,20 W
Rated current	0,30 A
Electrical connection	Elb fem conn M8, 8 pol

Ota yhteyttä Schmalziin

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Robots-Set ECBPMi

ROB-SET PLUS ECBPMi UR

Osanro.:10.03.01.00617

<https://www.schmalz.com/10.03.01.00617>

Operating temperature	0 ... 40 °C
Protection type IP	IP 40
for	Universal Robots
Product family	ROB-SET-ECBPM

Lisätarvikkeet



SLG FSGA 2 102x57

Osanro.:10.01.10.14043

Length L: 102 mm

Width B: 57 mm

Height H: 57 mm

Suction cup typ: FSGA

Number of suction cells: 2



SLG FSGA 3 102x102

Osanro.:10.01.10.14042

Length L: 102 mm

Width B: 102 mm

Height H: 57 mm

Suction cup typ: FSGA

Number of suction cells: 3

Robots-Set ECBPMi

ROB-SET PLUS ECBPMi UR

Osanro.:10.03.01.00617

<https://www.schmalz.com/10.03.01.00617>



SLG FSGA 4 102x75.3

Osanro.:10.01.10.14041

Length L: 102 mm

Width B: 75,3 mm

Height H: 57 mm

Suction cup typ: FSGA

Number of suction cells: 4

Varaosat



ECBPMi-RS-485 24V-DC FK

Osanro.:10.03.01.00584

Voltage DC: 24V - DC

Rated current: 0,3 A

Electrical connection: Spring contact

Inputs/outputs: RS 485

Operating temperature: 0 ... 40 °C

Suction rate (max.): 1,6 l/min

Rated power: 7,2 W



SPB1 30 ED-65 G1/4-AG

Osanro.:10.01.06.04530

Size: 30

Suction cup material: Elastodur ED

Material hardness [Shore A]: 65 Shore A

Thread G1: G1/4"-M

Number of folds: 1,5

Robots-Set ECBPMi

ROB-SET PLUS ECBPMi UR

Osanro.:10.03.01.00617

<https://www.schmalz.com/10.03.01.00617>



SFF 20 SI-55 G1/4-AG

Osanro.:10.01.01.14621

Size: 20

Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Material characteristics: FDA-compatible