

Connection set

SET MPL G1/4-IG

Part no...:10.01.27.01757

<https://www.schmalz.com/10.01.27.01757>

Home > Tehnologija vakuumskog stezanja > Clamping Equipment for Metal and Plastic Processing > Modular Clamping System MPL-ISST-SFM for Metal and Plastics Machining > SET MPL G1/4-IG

Connection set for hose connection



Construction use: Matrix-Plate

Connection: G1/4"-F

Design Data



Spare parts

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Connection set

SET MPL G1/4-IG

Part no.: 10.01.27.01757

<https://www.schmalz.com/10.01.27.01757>



HSV 7 3/2 G1/4-IG

Part no.: 10.05.07.00034

Nominal size: 7 mm

Function: 3/2-way valve

Thread G1: G1/4"-F

Pressure range (operating pressure): -0.95 ... 10.00 bar



VSL 10-7 PU MI-TR

Part no.: 10.07.09.00084

External diameter D: 10 mm

Internal diameter d: 7 mm

Length max.: 50 m

Material hose: PU

Bending radius min.: 60 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -40 ... 85 °C



ST G1/4-AG 13 MS-V

Part no.: 10.08.03.00158

Thread G1: G1/4"-M

Hose diameter (rec.) d: 13 mm

Material: Brass

Surface: nickel plated

Length L: 5,5 mm

Nominal diameter dn: 7,5 mm

Connection set

SET MPL G1/4-IG

Part no.:10.01.27.01757

<https://www.schmalz.com/10.01.27.01757>



STV-W G1/4-AG 10

Part no.:10.08.02.00254

Thread G1: G1/4"-M

Hose diameter: 10 mm

Material: Nickel plated

Operating temperature: -20 ... 80 °C

Length L: 27,2 mm



STV-GE G1/4-AG 10

Part no.:10.08.02.00251

Thread G1: G1/4"-M

Hose diameter: 10 mm

Material: Brass

Operating temperature: -20 ... 80 °C

External diameter D: 16,5 mm

Length L: 23,4 mm