

Sealing plug

VRS-STECH 10x18

Part no.:10.08.06.00060

<https://www.schmalz.com/10.08.06.00060>

Home > Vakuumska tehnologija za automatizaciju > Vacuum Components > Filters and Connections > Hoses and Connections > Screw in Push Fittings > VRS-STECH 10x18

Sealing plug




Operating temperature: °C

External diameter D: 10 mm

Length L: 18 mm

Design Data



Attribute	Value
D	10 mm
D1	10 mm
L	18 mm
L1	42 mm

Technical Data

Attribute	Value
Pressure range (operating pressure)	bar
Operating temperature	°C
Weight	2,10 g
Product family	STV

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si