

Spring plunger

FSTIm M5-IG M5-IG A 5 IN

Part no...:10.01.02.01480

<https://www.schmalz.com/10.01.02.01480>

Home > Vakuumska tehnologija za automatizaciju > Vacuum Components > Mounting Elements > Spring Plungers > Spring Plungers FSTIm > FSTIm M5-IG M5-IG A 5 IN

Spring plunger with internal damping spring and height compensation



Suction cup connection: M5-F


Vacuum connection: M5-F

Shape: Axial vacuum guide

Spring stroke Z: 5 mm

Shape mounting elements: (electrically) insulating

Design Data



Attribute	Value
dn	2 mm
G1	M5-F
G2	M5-F
G3	M10x1-M
H	42,40 mm
H2	14 mm
LG1	4,50 mm
LG2	4,50 mm
LG3	19 mm
SW1	14 mm
SW2	8 mm
Z (Stroke)	5 mm

Recommendation: Avoid maximum plunger stroke Z during continuous operation to extend service life Ensure that the hose guide is free from distortion

Technical Data

Attribute	Value
Shape mounting elements	(electrically) insulating
Spring rate	0,06 N/mm
Spring pretension	0,50 N
Spring force, center	0,64 N

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Spring plunger

FSTIm M5-IG M5-IG A 5 IN


Part no.:10.01.02.01480

<https://www.schmalz.com/10.01.02.01480>

Vertical load	15 N
Horizontal load	10 N
Weight	17,50 g
Operating temperature	0 ... 80 °C
Product family	FSTIm

Note: Spring force: Referred to 50 % of operating stroke Vertical loading: Maximum static loading Horizontal load: The specification of the horizontal load refers to the lower edge of the plunger with extended spring. It is a maximum static stress and it impairs the spring compression and extension in horizontal position.

Accessories



VSL 4-2.5 PU BL SO

Part no.:10.07.09.00142



ST M5-AG 4 MS-V

Part no.:10.08.03.00311

Thread G1: M5-M

Material: Brass

Surface: nickel plated

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Spring plunger

FSTIm M5-IG M5-IG A 5 IN

Part no...:10.01.02.01480

<https://www.schmalz.com/10.01.02.01480>



HTR-STA 47 1N D10/16 FL

Part no...:10.08.03.00085

Length L: 47 mm

Connection 1: Sliding block

Connection of suction cup, spring plunger: Contour D10 and D16

Shape: flat



HTR-ST5 30x30 D10/16 WI

Part no...:10.08.03.00088

Connection 1: 30x30

Connection of suction cup, spring plunger: Contour D10 and D16

Shape: angled



HTR-ST5 40x40 D10/16 WI

Part no...:10.08.03.00089

Connection 1: 40x40

Connection of suction cup, spring plunger: Contour D10 and D16

Shape: angled