

Tooling-System-Schmalz-Ejektor

SEAC 10 RP R

Part no.:10.02.02.03289

<https://www.schmalz.com/10.02.02.03289>

Home > Vakuumska tehnologija za automatizaciju > Vacuum Components > Vacuum Generators > Decentralized Ejectors > Ejectors With Blow Off System SEAC RP > SEAC 10 RP R

Tooling-System-Schmalz-Ejektor




Nozzle diameter: 1 mm

Function: pneumatic air-saving function

construction shape compact ejectors: Version right

Pressure range (operating pressure): 4.0 ... 6.0 bar

Design Data



Attribute	Value
B	44,50 mm
B3	14,20 mm
d	4,30 mm
d1	13,80 mm
D	27 mm
G1	G1/8"-F
G4	G1/8"-F
H	38,30 mm
H1	39,80 mm
H2	29,30 mm
L	52 mm
L2	29,50 mm
L3	8 mm
L4	22 mm
X1	28 mm

Technical Data

Attribute	Value
Nozzle diameter	1 mm
Degree of evacuation	85 %

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Tooling-System-Schmalz-Ejector

SEAC 10 RP R

Part no.:10.02.02.03289

<https://www.schmalz.com/10.02.02.03289>

Suction rate (max.)	36 l/min
Suction rate (max.)	2,10 m³/h
Air consumption suction	65 l/min
Air consumption suction	3,90 m³/h
Max. air consumption blow off	92 l/min
Pressure range (operating pressure)	4.0 ... 6.0 bar
Weight	180 g
Pressure range (operating pressure)	58.0 ... 87.0
Suction rate (max.)	1,27 cfm
Air consumption suction	2,30 cfm
Air consumption blow off	3,18 cfm
Max. vacuum	25,10 inHg
Product family	SEAC-RP

Note: Air consumption: At optimal operating pressure (4,5 bar)

Accessories



ADP-EJ 45.5x21x44-G1/4-IG SEAC VA-S

Part no.:10.02.02.03483

Length L: 45,5 mm

Width B: 21 mm

Height H: 44 mm

Thread G1: G1/4"-F

Construction use: Compact ejectors SEAC



ADP-EJ 45.5x21x44-G1/4-IG SEAC VA-L

Part no.:10.02.02.03484

Length L: 45,5 mm

Width B: 21 mm

Height H: 44 mm

Thread G1: G1/4"-F

Construction use: Compact ejectors SEAC

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Tooling-System-Schmalz-Ejector

SEAC 10 RP R

Part no...:10.02.02.03289

<https://www.schmalz.com/10.02.02.03289>



ADP-EJ 38x20x11-G1/4-IG SEAC

Part no...:10.02.02.04067

Length L: 38 mm

Width B: 20 mm

Height H: 11 mm

Thread G1: G1/4"-F

Construction use: Compact ejectors SEAC



ADP-EJ 38x20x11-G1/8-IG SEAC

Part no...:10.02.02.04068

Length L: 38 mm

Width B: 20 mm

Height H: 11 mm

Thread G1: G1/8"-F

Construction use: Compact ejectors SEAC



HT-SG A2 E 35 G1/4-AG

Part no...:10.07.06.00435

Connection 1: Bolt with slot Ø19mm

Shape: Ejector connection

Width B: 35 mm

Vacuum connection: G1/4"-F

Suction cup connection: G1/4"-M

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Tooling-System-Schmalz-Ejector

SEAC 10 RP R

Part no...:10.02.02.03289

<https://www.schmalz.com/10.02.02.03289>



HT-SG A2 E 35 G3/8-AG

Part no...:10.07.06.00441

Connection 1: Bolt with slot $\varnothing 19\text{mm}$

Shape: Ejector connection

Width B: 35 mm

Vacuum connection: G1/4"-F

Suction cup connection: G3/8"-M



HT-SG A2 E 46 RA

Part no...:10.07.06.00431

Connection 1: Bolt with slot $\varnothing 19\text{mm}$

Shape: Ejector connection

Width B: 46 mm

Vacuum connection: G1/4"-F

Suction cup connection: Rectangular adapter



HT-SG A3 E 35 G1/4-AG

Part no...:10.07.06.00338

Connection 1: Ball head 28.5 mm

Shape: Ejector connection

Width B: 35 mm

Vacuum connection: G1/4"-F

Suction cup connection: G1/4"-M

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Tooling-System-Schmalz-Ejector

SEAC 10 RP R

Part no...:10.02.02.03289

<https://www.schmalz.com/10.02.02.03289>



HT-SG A3 E 35 G3/8-AG

Part no...:10.07.06.00340

Connection 1: Ball head 28.5 mm

Shape: Ejector connection

Width B: 35 mm

Vacuum connection: G1/4\"-F

Suction cup connection: G3/8\"-M



HT-SG A3 E 46 RA

Part no...:10.07.06.00332

Connection 1: Ball head 28.5 mm

Shape: Ejector connection

Width B: 46 mm

Vacuum connection: G1/4\"-F

Suction cup connection: Rectangular adapter