

CobotPump

ECBPMi-RS-485 24V-DC FK

Part no.:10.03.01.00584

<https://www.schmalz.com/10.03.01.00584>

Home > Vakuumska tehnologija za automatizaciju > Vacuum Components > Vacuum Generators > Vacuum Generators End-of-Arm > ECBPMi-RS-485 24V-DC FK

CobotPump (Mini) for electrical vacuum generation for collaborative robots



Voltage DC: 24V - DC

Rated current: 0,3 A

Electrical connection: Spring contact


Inputs/outputs: RS 485

Operating temperature: 0 ... 40 °C

Suction rate (max.): 1,6 l/min

Rated power: 7,2 W

Design Data



Attribute	Value
D	63 mm
D2	35,50 mm
D mk1	46 mm
G1	M4-F
G2	G1/4"-F
L	56,40 mm
L1	61,40 mm
LG1	6 mm
LG2	11 mm

Technical Data

Attribute	Value
Suction rate (max.)	1,60 l/min
Voltage DC	24V - DC
Rated power	7,20 W
Rated current	0,30 A
Electrical connection	Spring contact
Operating temperature	0 ... 40 °C

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si