

Bellows suction cup (round)

FG 18 NBR-ESD-55 N062

Part no.:10.01.06.04458

<https://www.schmalz.com/10.01.06.04458>

Home > Vakuumska tehnologija za automatizaciju > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Round) > FG 18 NBR-ESD-55 N062

Bellows suction cup (round) for very uneven workpieces




Size: 18

Suction cup material: Nitrile rubber NBR-ESD

Material hardness [Shore A]: 55 Shore A

Number of folds: 2,5

Design Data



Attribute	Value
d	4,50 mm
d2	8 mm
D1	17,80 mm
Dk	10 mm
Dmax(S)	19 mm
Ds	17,20 mm
H	22,60 mm
H2	3,80 mm
H3	9 mm
Z (Stroke)	9 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	3,02 N
Pull-off force	8,50 N
Volume	1,65 cm ³
Curve radius (min) (convex)	20 mm
Size	18
Number of folds	2,50
Suction cup material	Nitrile rubber NBR-ESD

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Bellows suction cup (round)

FG 18 NBR-ESD-55 N062

Part no.:10.01.06.04458

<https://www.schmalz.com/10.01.06.04458>

Material hardness [Shore A]

55 Shore A

Weight

1,90 g

Product family

FG

Accessories



SA-NIP N062 M5-AG DN250

Part no.:10.01.06.05668

Thread G1: M5-M

Length L1: 15,9 mm

Fitting length: 5 mm

Nominal diameter dn: 2,5 mm

Material: Aluminum



SA-NIP N062 G1/8-IG DN350

Part no.:10.01.06.05669

Thread G1: G1/8"-F

Length L1: 17,9 mm

Fitting length: 12 mm

Nominal diameter dn: 3,5 mm

Material: Aluminum



SA-NIP N062 G1/8-AG DN350

Part no.:10.01.06.05670

Thread G1: G1/8"-M

Length L1: 19,4 mm

Fitting length: 6 mm

Nominal diameter dn: 3,5 mm

Material: Aluminum

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Bellows suction cup (round)

FG 18 NBR-ESD-55 N062

Part no...:10.01.06.04458

<https://www.schmalz.com/10.01.06.04458>
