

Bellows suction cup HT2 (round)

SAB 40 HT2-65 G3/8-IG

Part no.:10.01.06.02429

<https://www.schmalz.com/10.01.06.02429>

Home > Vakuumska tehnologija za automatizaciju > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Round) > Bellows Suction Cups SAB HT2 (1.5 Folds) > SAB 40 HT2-65 G3/8-IG

Bellows suction cup (round) for handling hot workpieces



Size: 40

Suction cup material: High temperature material HT2

Material hardness [Shore A]: 65 Shore A


Temperature resistance: 200 °C

Nipple material: Nickel plated

Connection: G3/8-IG

Number of folds: 1,5

Design Data



Attribute	Value
dn	4 mm
D1	32 mm
Dmax(S)	45 mm
Ds	40,10 mm
G1	G3/8"-F
H	44 mm
LG1	9,50 mm
SW1	22 mm
Z (Stroke)	10 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	38 N
Pull-off force	59 N
Lateral force	34 N
Volume	7 cm ³
Curve radius (min) (convex)	40 mm
Hose diameter (rec.) d	4 mm
Size	40
Connection	G3/8"-F

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Bellows suction cup HT2 (round)

SAB 40 HT2-65 G3/8-IG

Part no.:10.01.06.02429

<https://www.schmalz.com/10.01.06.02429>

Suction cup material	High temperature material HT2
Material hardness [Shore A]	65 Shore A
Weight	50,20 g
Number of folds	1,50
Product family	SAB