

Flat suction cup (round)

PFG 3.5 NBR-CO-55 N003

Part no.:10.01.01.10042

<https://www.schmalz.com/10.01.01.10042>

Home > Vakuumska tehnologija za automatizaciju > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > PFG 3.5 NBR-CO-55 N003

Flat suction cup (round) for smooth or slightly rough surfaces




Size: 3,5

Suction cup material: Nitrile rubber NBR-conductive

Material hardness [Shore A]: 55 Shore A

Design Data



Attribute	Value
d	2 mm
d1	3 mm
Dk	4,20 mm
Dmax(S)	4 mm
Ds	3,50 mm
H	4 mm
H2	1,50 mm
H3	2,50 mm
Z (Stroke)	0,50 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	0,42 N
Volume	0,02 cm ³
Curve radius (min) (convex)	7,50 mm
Size	3,50
Nipple family	N 003
Suction cup material	Nitrile rubber NBR-conductive
Material hardness [Shore A]	55 Shore A

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Flat suction cup (round)

PFG 3.5 NBR-CO-55 N003

Part no...:10.01.01.10042

<https://www.schmalz.com/10.01.01.10042>

Product family

PFG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



SA-NIP N003 M3-AG DN100

Part no...:10.01.01.00316

Thread G1: M3-M

Length L1: 7,5 mm

Fitting length: 2 mm

Material: Aluminum