

Flat suction cup (round)

PFYN 150 NBR-55 G1/2-IG

Part no.:10.01.01.00339

<https://www.schmalz.com/10.01.01.00339>

Home > Vakuumska tehnologija za automatizaciju > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > Flat Suction Cups
PFYN > PFYN 150 NBR-55 G1/2-IG

Flat suction cup (round) for smooth or slightly rough surfaces



Size: 150


Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Nipple material: Aluminum

Vacuum connection: G1/2"-F

Design Data



Attribute	Value
dn	13,50 mm
Dmax(S)	158 mm
Ds	147,50 mm
G1	G1/2"-F
H	45,50 mm
LG1	13 mm
Z (Stroke)	9 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	842 N
Volume	176,30 cm ³
Curve radius (min) (convex)	300 mm
Hose diameter (rec.) d	9 mm
Size	150
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55 Shore A

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Flat suction cup (round)

PFYN 150 NBR-55 G1/2-IG

Part no.:10.01.01.00339

<https://www.schmalz.com/10.01.01.00339>

Weight 521,40 g

Product family PFYN

Number of folds 0

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



SU 160

Part no.:10.01.01.12438

Size: 160

Clamping range: 150.0 ... 180.0 mm

Temperature resistance: 80 °C

Spare parts



SA-NIP N010 G1/2-IG

Part no.:10.01.01.00796

Thread G1: G1/2"-F

Material: Aluminum

Flat suction cup (round)

PFYN 150 NBR-55 G1/2-IG

Part no...:10.01.01.00339

<https://www.schmalz.com/10.01.01.00339>



PFG 150 NBR-55 N010

Part no...:10.01.01.00333

Size: 150

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A