

Flat suction cup (round)

SHF 70 NK-45 N041

Part no.:10.01.01.11682

<https://www.schmalz.com/10.01.01.11682>

Flat suction cup (round) for highly dynamic handling of wood




Size: 70

Suction cup material: Natural Rubber NK

Material hardness [Shore A]: 45 Shore A

Design Data



Attribute	Value
d	7,50 mm
d1	17 mm
d2	48 mm
Dk	17 mm
Dmax(S)	74 mm
Ds	70 mm
H	22,20 mm
H2	12,80 mm
H3	14,30 mm
Z (Stroke)	4 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Size	70
Nipple family	N 041
Number of folds	0
Lateral force	145 N
Suction force (-600mbar)	155 N
Suction cup material	Natural Rubber NK
Volume	16,21 cm ³
Curve radius (min) (convex)	95 mm

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Flat suction cup (round)

SHF 70 NK-45 N041

Part no...:10.01.01.11682

<https://www.schmalz.com/10.01.01.11682>

Weight	28,20 g
Product family	SHF

Accessories



SA-NIP N041 G1/4-AG DN440

Part no...:10.01.01.11772

Thread G1: G1/4"-M

Fitting length: 4 mm

Material: Aluminum



SA-NIP N041 G1/4-IG DN440

Part no...:10.01.01.11822

Thread G1: G1/4"-F

Fitting length: 15 mm

Material: Aluminum



SIEB 15x0.8 MS-A2 0.103/0.07

Part no...:10.07.01.00211

External diameter D: 15 mm

Length L: 0,8 mm

Material: Brass / Stainless steel

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Flat suction cup (round)

SHF 70 NK-45 N041

Part no...:10.01.01.11682

<https://www.schmalz.com/10.01.01.11682>



TVN G1/4-AG 8.4 N041

Part no...:10.05.10.00058

Thread G1: G1/4"-M

Spring stroke Z: 8,4 mm

Nipple: N 041