

Flat suction cup (round)

SUF 15 SI-55 G1/8-AG

Part no.:10.01.01.14129

<https://www.schmalz.com/10.01.01.14129>

Home > Vakuumska tehnologija za automatizaciju > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > Flat Suction Cups
SUF > SUF 15 SI-55 G1/8-AG

Flat suction cup (round) for process safe handling of smooth or slightly rough surfaces



Size: 15


Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Material characteristics: FDA-compatible

Vacuum connection: G1/8"-M

Design Data



Attribute	Value
Dmax(S)	16,80 mm
Ds	15 mm
dn	3,10 mm
G1	G1/8"-M
H	15 mm
LG1	7,50 mm
SW1	14 mm
Z (Stroke)	1,50 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	9 N
Pull-off force	9 N
Volume	0,22 cm ³
Curve radius (min) (convex)	20 mm
Hose diameter (rec.) d	4 mm
Size	15
Suction cup material	Silicone SI
Material hardness [Shore A]	55 Shore A

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Flat suction cup (round)

SUF 15 SI-55 G1/8-AG

Part no.:10.01.01.14129

<https://www.schmalz.com/10.01.01.14129>

Weight	4,70 g
Product family	SUF
Number of folds	0

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare parts



SC 030 G1/8-AG

Part no.:10.01.06.04288

Connection geometry: 030

Vacuum connection: G1/8"-M

Fitting length: 6 mm

Nominal diameter dn: 3,1 mm



SUF 15 SI-55 SC030

Part no.:10.01.01.13967

Size: 15

Suction cup material: Silicone SI

Material characteristics: FDA-compatible

Material hardness [Shore A]: 55 Shore A