

Bell suction cup (oval)

SAOG-S 95x40 NBR-60 G1/8-IG

Part no.:10.01.01.12180

<https://www.schmalz.com/10.01.01.12180>

Home > Vakuumska tehnologija za automatizaciju > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Sheet Metal > Bell-Shaped Suction Cups SAOG-S > SAOG-S 95x40 NBR-60 G1/8-IG

Bell suction cup (oval) for very dynamic handling of smooth and oily workpieces



Dimensions (LxB): 95x40

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 60 Shore A

Nipple material: Aluminum

Connection: G1/8-IG

Design Data



Attribute	Value
Bmax(S)	46 mm
Bs	40,60 mm
G1	G1/8"-F
H	15 mm
LG1	5 mm
Lmax(S)	101 mm
Ls	95,60 mm
Z (Stroke)	6 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	165 N
Lateral force	192 N
Lateral force (oily surface)	110 N
Volume	18 cm ³
Curve radius (min) (convex)	35 mm
Hose diameter (rec.) d	6 mm
Dimensions (LxB)	95 x 40
Suction cup material	Nitrile rubber NBR

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Bell suction cup (oval)

SAOG-S 95x40 NBR-60 G1/8-IG

Part no...:10.01.01.12180

<https://www.schmalz.com/10.01.01.12180>

Number of folds	0
Weight	32,80 g
Product family	SAOG-S