

Flat suction pad (round)

SFF 10 HT1-60 M5-AG

Part no.:10.01.01.14272

<https://www.schmalz.com/10.01.01.14272>

Home > Vakuumska tehnologija za automatizaciju > Vacuum Components > Vacuum Suction Cups > Suction Cups for Plastic Films and Paper > Suction Cups SFF / SFB1 > SFF 10 HT1-60 M5-AG

Flat suction cup (round) for dynamic handling of thin and flexible workpieces



Size: 10

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A

Number of folds: 0

Design Data



Attribute	Value
G1	M5-M
Dmax(S)	11 mm
Ds	10 mm
dn	1,80 mm
LG1	4,70 mm
H	15,40 mm
SW1	8 mm
Z (Stroke)	0,70 mm

Technical Data

Attribute	Value
Size	10
Suction cup material	High temperature material HT1
Suction force (-600mbar)	2,70 N
Product family	SFF
Volume	0,25 cm ³
Number of folds	0
Material hardness [Shore A]	60 Shore A

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Flat suction pad (round)

SFF 10 HT1-60 M5-AG

Part no.:10.01.01.14272

<https://www.schmalz.com/10.01.01.14272>

Spare parts



SFF 10 HT1-60 SC030

Part no.:10.01.01.14050

Size: 10

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A

Number of folds: 0



SC 030 M5-AG

Part no.:10.01.06.02802

Connection geometry: 030

Connection: M5-M

Length L1: 15,5 mm

Fitting length: 5 mm

Nominal diameter dn: 1,8 mm