

Flat suction cup (round)


SPF 15 ED-65 SC040

Part no.:10.01.01.12895

<https://www.schmalz.com/10.01.01.12895>

Home > Vakuumska tehnologija za automatizaciju > Vacuum Components > Vacuum Suction Cups > Suction Cups for the Packaging Industry > SPF 15 ED-65 SC040

Flat suction cup (round) for dynamic handling of cardboard and rigid packaging




Size: 15

Suction cup material: Elastodur ED

Material hardness [Shore A]: 65 Shore A

Height H: 10 mm

Design Data



Attribute	Value
d	7,50 mm
d1	10,40 mm
Dk	13 mm
Dmax(S)	18,50 mm
Ds	16,40 mm
H	10 mm
H2	4,60 mm
Z (Stroke)	1,50 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	9,80 N
Pull-off force	11 N
Lateral force	7,90 N
Volume	0,76 cm ³
Curve radius (min) (convex)	13 mm
Hose diameter (rec.) d	4 mm
Size	15

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Flat suction cup (round)

SPF 15 ED-65 SC040

Part no.:10.01.01.12895

<https://www.schmalz.com/10.01.01.12895>

Nipple family	SC 040
Number of folds	0
Suction cup material	Elastodur ED
Material hardness [Shore A]	65 Shore A
Weight	0,70 g
Product family	SPF

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



SC 040 NPT1/8-AG

Part no.:10.01.06.02541

Connection geometry: 040

Connection: NPT1/8-M

Length L1: 20,9 mm

Fitting length: 6 mm

Nominal diameter dn: 4,1 mm



SC 040 NPT1/8-IG

Part no.:10.01.06.02542

Connection geometry: 040

Connection: NPT1/8-F

Length L1: 20,7 mm

Fitting length: 14 mm

Nominal diameter dn: 4,1 mm

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si