

Solenoid valve

EMVP 20 230V-AC 3/2 NO/NC

Part no.:10.05.02.00148

<https://www.schmalz.com/10.05.02.00148>

Home > Vakuumska tehnologija za automatizaciju > Vacuum Components > Valve Technology > Solenoid Valves > Solenoid Valves EMVP > EMVP 20 230V-AC 3/2 NO/NC

Solenoid valve EMVP for vacuum, pneumatic pilot control



Nominal size: 20 mm

Voltage DC: 230V - AC

Function: 3/2-way valve

Control valve: Optional NO/NC


Connecting thread: G3/4"-F

Pressure range (operating pressure): bar

Nominal flow rate: 40 m³/h

Weight: 0,37 kg

Design Data



Attribute	Value
B	75 mm
B1	77,50 mm
B2	37,50 mm
d	6,50 mm
D	80 mm
G1	G3/4"-F
G2	G3/4"-F
G3	G3/4"-F
G4	G1/8"-F
H	166,30 mm
H1	178,30 mm
H2	22,50 mm
L	75 mm
L1	115,50 mm
X1	63 mm
Y1	32,50 mm

Technical Data

Attribute	Value
Nominal size	20 mm
Nominal flow rate	40 m ³ /h

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Solenoid valve


EMVP 20 230V-AC 3/2 NO/NC

Part no.:10.05.02.00148

<https://www.schmalz.com/10.05.02.00148>

Control valve	Optional NO/NC
Nominal flow rate	667 l/min
Power consumption DC	5 W
Voltage DC	230V - AC
Closing time	90 ms
Weight	0,37 kg
Product family	EMVP

Accessories



FAS 80x39 G3/4-AG

Part no.:10.05.01.00062

External diameter D: 80 mm

Length L: 39 mm

Thread G1: G3/4"-M