

Robots-Set FXCB

ROB-SET FXCB UR O20

부품 번호...10.01.43.00064

<https://www.schmalz.com/10.01.43.00064>

홈페이지 > 진공 자동화 기술 > 진공 부품 > 광영역 그리핑 시스템 및 엔드 이펙터 > 광영역 그리핑 시스템 FXCB/FMCB > Handling Sets FXCB > ROB-SET FXCB UR O20

Complete vacuum system for connecting to lightweight robots




for: Universal Robots

Type: 3,5,10,16

Construction shape vacuum switch: NPN switching

Control valve: Normally open

디자인 데이터



속성	값
B	130 mm
B1	159 mm
H	131.40 mm
H1	137.40 mm
H2	20 mm
L	300 mm
L1	331 mm
L2	99 mm
L3	102 mm
dn	10 mm

기술 데이터

속성	값
Weight	2 kg
Suction rate (max.)	525.90 l/min
Material type	Foam O, Height 20 mm
Number of suction cells	45
Lift capacity (vertical)	80 N
Max. load (horizontal)	350 N
for	Universal Robots
Product family	ROB-SET-FXCB

Schmalz에 문의

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8462403 |...에서 3
schmalz@schmalz.co.kr

Robots-Set FXCB

ROB-SET FXCB UR O20

부품 번호...10.01.43.00064

<https://www.schmalz.com/10.01.43.00064>

The technical properties of the robot types may vary by region. The stated compatibility of the set is based on standard European models.

예비 부품



MASK-FOL SW110 294 3R18 FLGR

부품 번호...10.01.11.03375

Length L: 294 mm

Width B: 109.8 mm

Height H: 0.39 mm

Construction use: Vacuum area gripping system

Arrangement: 3R18

Nozzle diameter: 1.1 mm



EMVP 2.35 24V-DC 2x3/2 NO/NC CAR

부품 번호...10.01.11.03420

Length L: 82.1 mm

Width B: 53.7 mm

Height H: 10.8 mm



DI-PL 300x130 3R18 LL-20x7 O20 KE

부품 번호...10.01.11.03658

Length L: 300 mm

Width B: 130 mm

Height H: 20 mm

Construction use: Vacuum area gripping system

Arrangement: 3R18

Add. function: Adhesive tape on one side

Schmalz에 문의

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8462402 |...에서 3
schmalz@schmalz.co.kr

Robots-Set FXCB

ROB-SET FXCB UR O20

부품 번호...10.01.43.00064

<https://www.schmalz.com/10.01.43.00064>



SD 97x34x20 FXCB

부품 번호...10.01.43.00005

Length L: 97 mm

Width B: 34 mm

Height H: 20 mm



VSi V D M8-4

부품 번호...10.06.02.00577

Measuring range: -1,0 ... 0,0 bar

Construction shape vacuum switch: with display

Electrical connection: Male connect M8, 4 pole

Indication: 2xLED

Protection type IP: IP 65