

평 패드

FMP-SVK 1036 5R18 O10O10 F G60

부품 번호...10.01.38.03074

<https://www.schmalz.com/10.01.38.03074>


홈페이지 > 진공 자동화 기술 > 진공 부품 > 광영역 그리핑 시스템 및 엔드 이펙터 > 광영역 그리핑 시스템 FXP/FMP > 광영역 그리핑 시스템 FMP > FMP-SVK 1036 5R18 O10O10 F G60

볼 체크 밸브가 있는 외부 진공 발생 장치용 광영역 진공 그리퍼 시스템



Length L: 1,036 mm
Width B: 130 mm
Arrangement: 5R18
Material type: Foam O, Height 2x10 mm
Add. function: Filter
construction shape fittings: Straight
External diameter D: 60 mm
Weight: 4.4 kg
Product family: FMP

디자인 데이터



속성	값
B	130 mm
B3	21.60 mm
D	60 mm
H	70 mm
H1	116 mm
H2	20 mm
H3	7.70 mm
H4	5.50 mm
H5	46 mm
L	1036 mm
L2	996 mm
L3	90 mm
Y1	90 mm
Valve type	SVK

참고: 치수 D에 해당하는 내경의 진공 호스가 필요합니다. 기술 데이터 참조 -> 모양

기술 데이터

속성	값
Arrangement	5R18
Material type	Foam O, Height 2x10 mm
Number of suction cells	275

Schmalz에 문의

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8462403 |...에서
schmalz@schmalz.co.kr

평 패드

FMP-SVK 1036 5R18 O10O10 F G60

부품 번호...:10.01.38.03074

<https://www.schmalz.com/10.01.38.03074>

Suction force at -250 mbar 1055 N

Add. function Filter

Add. function Filter

Weight 4.40 kg

Sealing element Sealing Foam

Evacuation rate for $p_u = -0,25$ bar 750 l/min

Product family FMP

For compressed air with 5.5 bar input pressure At -0.25 bar and with the gripper fully covered by a workpiece typical for the application (wooden board with structured surface) The external vacuum generator used must supply at least the specified suction flow (at the vacuum connection piece of the FMP) at -0.25 bar but max. 135 % of the specified suction flow

부속품



ABDK-PROF-10x7x1450-KU-SW-FXP-FMP

부품 번호...:26.07.03.00002

Length L: 1,450 mm

Width B: 10 mm

Height H: 7 mm

Material: Plastics

Measuring range: bar

Construction use: Vacuum area gripping system FXP-FMP



EMVP 50 24V-DC 3/2 NO

부품 번호...:10.05.02.00069

Nominal size: 50 mm

Voltage DC: 24V - DC

Function: 3/2-way valve

Control valve: Normally open

Connecting thread: G2"-F

Pressure range (operating pressure): bar

Nominal flow rate: 310 m³/h

Weight: 1.36 kg

Schmalz에 문의

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8462402 |...에서 schmalz@schmalz.co.kr

평 패드

FMP-SVK 1036 5R18 O10O10 F G60

부품 번호...10.01.38.03074

<https://www.schmalz.com/10.01.38.03074>



FLAN-PL 120x85x10 ST FLGR

부품 번호...10.01.10.05701

Length L: 120 mm

Width B: 85 mm

Height H: 10 mm

Material: Steel

Construction use: Vacuum area gripping system



FLK G1/2-IG G1/2-AG

부품 번호...10.01.03.00175

Thread G1: G1/2"-F

Thread G2: G1/2"-M

Operating temperature: 0 ... 70 °C



FST-FLEX 25 HD1 G1/2-AG G3/8-IG

부품 번호...10.01.10.05697

Spring stroke Z: 25 mm

Shape mounting elements: Heavy Duty 1 spring plunger

Construction use: Mounting section

평 패드

FMP-SVK 1036 5R18 O10O10 F G60

부품 번호...10.01.38.03074

<https://www.schmalz.com/10.01.38.03074>



FST-FLEX 25 HD2 G1/2-AG G3/8-IG

부품 번호...10.01.10.05695

Spring stroke Z: 25 mm

Shape mounting elements: Heavy Duty 2 spring plunger

Construction use: Mounting section



FST-FLEX 50 HD1 G1/2-AG G3/8-IG

부품 번호...10.01.10.05687

Spring stroke Z: 50 mm

Shape mounting elements: Heavy Duty 1 spring plunger

Construction use: Mounting section



FST-FLEX 50 HD2 G1/2-AG G3/8-IG

부품 번호...10.01.10.05168

Spring stroke Z: 50 mm

Shape mounting elements: Heavy Duty 2 spring plunger

Construction use: Mounting section

평 패드

FMP-SVK 1036 5R18 O10O10 F G60

부품 번호...10.01.38.03074

<https://www.schmalz.com/10.01.38.03074>



FST-FLEX 75 HD1 G1/2-AG G3/8-IG

부품 번호...10.01.10.05698

Spring stroke Z: 75 mm

Shape mounting elements: Heavy Duty 1 spring plunger

Construction use: Mounting section



FST-FLEX 75 HD2 G1/2-AG G3/8-IG

부품 번호...10.01.10.05696

Spring stroke Z: 75 mm

Shape mounting elements: Heavy Duty 2 spring plunger

Construction use: Mounting section



FST-STARR 25 HD1 G1/2-AG G3/8-IG

부품 번호...10.01.10.05810

Spring stroke Z: 25 mm

Shape mounting elements: Heavy Duty 1 spring plunger

Construction use: Mounting section

평 패드

FMP-SVK 1036 5R18 O10O10 F G60

부품 번호...10.01.38.03074

<https://www.schmalz.com/10.01.38.03074>



FST-STARR 25 HD2 G1/2-AG G3/8-IG

부품 번호...10.01.10.05806

Spring stroke Z: 25 mm

Shape mounting elements: Heavy Duty 2 spring plunger

Construction use: Mounting section



FST-STARR 50 HD1 G1/2-AG G3/8-IG

부품 번호...10.01.10.05809

Spring stroke Z: 50 mm

Shape mounting elements: Heavy Duty 1 spring plunger

Construction use: Mounting section



FST-STARR 50 HD2 G1/2-AG G3/8-IG

부품 번호...10.01.10.05805

Spring stroke Z: 50 mm

Shape mounting elements: Heavy Duty 2 spring plunger

Construction use: Mounting section

평 패드

FMP-SVK 1036 5R18 O10O10 F G60

부품 번호...10.01.38.03074

<https://www.schmalz.com/10.01.38.03074>



FST-STARR 75 HD1 G1/2-AG G3/8-IG

부품 번호...10.01.10.05808

Spring stroke Z: 75 mm

Shape mounting elements: Heavy Duty 1 spring plunger

Construction use: Mounting section



FST-STARR 75 HD2 G1/2-AG G3/8-IG

부품 번호...10.01.10.05803

Spring stroke Z: 75 mm

Shape mounting elements: Heavy Duty 2 spring plunger

Construction use: Mounting section



MOD-FLAN 120x120 FXP-FMP

부품 번호...10.01.21.00244

Length L: 120 mm

Width B: 120 mm

Height H: 60 mm

Weight: 1.1 kg

Measuring range: bar


Construction use: Vacuum area gripping system FXP-FMP

평 패드

FMP-SVK 1036 5R18 O10O10 F G60

부품 번호...10.01.38.03074

<https://www.schmalz.com/10.01.38.03074>



SET fuer-Sensor(FXP/FMP)

부품 번호...10.01.38.01194



SET FXC-FMC

부품 번호...10.01.21.01291

Length L: 119 mm

Width B: 119 mm

Height H: 9.6 mm

Measuring range: bar

Construction use: Vacuum area gripping system FXC-FMC



SET FXP-FMP

부품 번호...10.01.21.02407

Length L: 232 mm

Width B: 119 mm

Height H: 119 mm

Measuring range: bar

Construction use: Vacuum area gripping system FXP-FMP

평 패드

FMP-SVK 1036 5R18 O10O10 F G60

부품 번호...10.01.38.03074

<https://www.schmalz.com/10.01.38.03074>



SET FXP-FMP 4NUTSTEIN

부품 번호...10.01.21.00243

contains: 4 slot nuts

Measuring range: bar

Construction use: Vacuum area gripping system FXP-FMP



STF 60 P 4.5 SSD

부품 번호...10.07.01.00259

Connection: Ø60mm

Shape: Piclon housing

Nominal flow rate: 270 m³/h

Filter pore size: 3 µm

Additional function: Hose clamps SSD



VAM 40 V U BAR

부품 번호...10.07.02.00046

External diameter D: 40 mm

Measuring range: -1,00 ... 0,00 bar

평 패드

FMP-SVK 1036 5R18 O10O10 F G60

부품 번호...10.01.38.03074

<https://www.schmalz.com/10.01.38.03074>



VENT-EINH 8/6 NC 24V-DC

부품 번호...10.01.21.02405

Construction use: Vacuum area gripping system FXP-FMP

Connection: Hose 8/6

Control valve: Normally closed



VSL 71-60 PU-DS-AS TR

부품 번호...10.07.09.00034

External diameter D: 71 mm

Internal diameter d: 60 mm


Length max.: 20 m

Material hose: PU, wire spiral, antistatic

Bending radius min.: 40 mm

Pressure range (operating pressure): -0.69 ... 2.09 bar

Operating temperature: -40 ... 90 °C



VS-MONT 50x15.8x25 VS

부품 번호...10.06.02.00343

Length L: 50 mm

Width B: 15.8 mm

Height H: 25 mm

Measuring range: bar

Construction use: Vacuum switch

평 패드

FMP-SVK 1036 5R18 O10O10 F G60

부품 번호...10.01.38.03074

<https://www.schmalz.com/10.01.38.03074>



VS-MONT 76.5x19 VSi FXP-FMP

부품 번호...10.01.38.02485

Length L: 76.5 mm

Width B: 19 mm

Add. function: Vacuum and pressure switch VSi

Measuring range: bar

Add. function: Vacuum and pressure switch

Construction use: Vacuum area gripping system FXP-FMP



VTR-SL 3x RST60

부품 번호...10.01.10.02779

Length L: 439 mm

Width B: 100 mm

Height H: 156 mm

Connection: Tube end Ø60



FLAN-PL 120x120x10 FXC-FMC

부품 번호...10.01.21.00313

Length L: 120 mm

Width B: 120 mm

Height H: 10 mm

Measuring range: bar

Construction use: Vacuum area gripping system FXC-FMC

평 패드

FMP-SVK 1036 5R18 O10O10 F G60

부품 번호...10.01.38.03074

<https://www.schmalz.com/10.01.38.03074>



FLK G1/2-IG G1/2-AG V

부품 번호...10.01.03.00207

Thread G1: G1/2"-F

Thread G2: G1/2"-M

Operating temperature: 0 ... 70 °C

Shape mounting elements: Reinforced

예비 부품



MASK-FOL SVK 996 5R18 FXP-FMP

부품 번호...10.01.38.02393

Length L: 996 mm

Width B: 109.8 mm

Height H: 0.4 mm

Measuring range: bar

Construction use: Vacuum area gripping system FXP-FMP



DI-PL 1036-5R18 O10O10 F FXP-FMP

부품 번호...10.01.38.02176

Length L: 1,036 mm

Width B: 128 mm

Height H: 20 mm

Arrangement suction cells: 5 rows, 18 mm

Material type: Foam O, Height 2x10 mm

Add. function: Filter

Measuring range: bar

Construction use: Vacuum area gripping system FXP-FMP