

평 패드

FXP-SW70 442 3R18 O10O10 F

부품 번호...10.01.38.00690

<https://www.schmalz.com/10.01.38.00690>

홈페이지 > 진공 자동화 기술 > 진공 부품 > 광영역 그리핑 시스템 및 엔드 이펙터 > 광영역 그리핑 시스템 FXP/FMP > 영역 그 리핑 시스템 FXP > FXP-SW70 442 3R18 O10O10 F

통합형 공압식 진공 발생 장치와 플로우 레지스터가 있는 광영역 진공 그리퍼 시스템



Length L: 442 mm

Width B: 130 mm

Arrangement: 3R18

Material type: Foam O, Height 2x10 mm

Add. function: Filter

Number of suction cells: 66

Design: Multi-stage ejector SEMP


Nozzle diameter: 0.7 mm

Air consumption: 250 l/min

Weight: 2.5 kg

Product family: FXP

디자인 데이터



속성

값

B	130 mm
B3	21.60 mm
H	70 mm
H1	109 mm
H2	20 mm
H3	7.70 mm
H4	5.50 mm
H5	28 mm
L	442 mm
L2	402 mm
L3	154 mm
Y1	90 mm
Valve type	SW

Permissible dimensional tolerances for elastomer parts according to DIN ISO 3302-1 M3 Note: Two ejectors/silencer box covers are used for the 1,234 mm and 1,432 mm lengths. Type FXP requires compressed air hose 12/9 mm

기술 데이터

속성	값
Arrangement	3R18

Schmalz에 문의

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8402403 |...에서 schmalz@schmalz.co.kr

평 패드

FXP-SW70 442 3R18 O10O10 F

부품 번호...10.01.38.00690

<https://www.schmalz.com/10.01.38.00690>

Material type	Foam O, Height 2x10 mm
Number of suction cells	66
Suction force at -250 mbar	440 N
Suction rate (max.)	1050 l/min
Air consumption	250 l/min
Sealing element	Sealing Foam
Add. function	Filter
Add. function	Filter
Weight	2.50 kg
Product family	FXP

Sound level: 74 dB(A) Max. degree of evacuation 55%

부속품



VENT-EINH 8/6 NC 24V-DC

부품 번호...10.01.21.02405

Construction use: Vacuum area gripping system FXP-FMP

Connection: Hose 8/6

Control valve: Normally closed



VENT-EINH NO 24V-DC 1

부품 번호...10.01.38.01101

Construction use: Vacuum area gripping system FXP


Control valve: Normally open

평 패드

FXP-SW70 442 3R18 O10O10 F

부품 번호...10.01.38.00690

<https://www.schmalz.com/10.01.38.00690>



FLAN-PL 120x85x10 ST FLGR

부품 번호...10.01.10.05701

Length L: 120 mm

Width B: 85 mm

Height H: 10 mm

Material: Steel

Construction use: Vacuum area gripping system



FLK G1/2-IG G1/2-AG

부품 번호...10.01.03.00175

Thread G1: G1/2"-F

Thread G2: G1/2"-M

Operating temperature: 0 ... 70 °C



FST-FLEX 25 HD1 G1/2-AG G3/8-IG

부품 번호...10.01.10.05697

Spring stroke Z: 25 mm

Shape mounting elements: Heavy Duty 1 spring plunger

Construction use: Mounting section

평 패드

FXP-SW70 442 3R18 O10O10 F

부품 번호...10.01.38.00690

<https://www.schmalz.com/10.01.38.00690>



FST-FLEX 25 HD2 G1/2-AG G3/8-IG

부품 번호...10.01.10.05695

Spring stroke Z: 25 mm

Shape mounting elements: Heavy Duty 2 spring plunger

Construction use: Mounting section



FST-FLEX 50 HD1 G1/2-AG G3/8-IG

부품 번호...10.01.10.05687

Spring stroke Z: 50 mm

Shape mounting elements: Heavy Duty 1 spring plunger

Construction use: Mounting section



FST-FLEX 50 HD2 G1/2-AG G3/8-IG

부품 번호...10.01.10.05168

Spring stroke Z: 50 mm

Shape mounting elements: Heavy Duty 2 spring plunger

Construction use: Mounting section

평 패드

FXP-SW70 442 3R18 O10O10 F

부품 번호...10.01.38.00690

<https://www.schmalz.com/10.01.38.00690>



FST-FLEX 75 HD1 G1/2-AG G3/8-IG

부품 번호...10.01.10.05698

Spring stroke Z: 75 mm

Shape mounting elements: Heavy Duty 1 spring plunger

Construction use: Mounting section



FST-FLEX 75 HD2 G1/2-AG G3/8-IG

부품 번호...10.01.10.05696

Spring stroke Z: 75 mm

Shape mounting elements: Heavy Duty 2 spring plunger

Construction use: Mounting section



FST-STARR 25 HD1 G1/2-AG G3/8-IG

부품 번호...10.01.10.05810

Spring stroke Z: 25 mm

Shape mounting elements: Heavy Duty 1 spring plunger

Construction use: Mounting section

평 패드

FXP-SW70 442 3R18 O10O10 F

부품 번호...10.01.38.00690

<https://www.schmalz.com/10.01.38.00690>



FST-STARR 25 HD2 G1/2-AG G3/8-IG

부품 번호...10.01.10.05806

Spring stroke Z: 25 mm

Shape mounting elements: Heavy Duty 2 spring plunger

Construction use: Mounting section



FST-STARR 50 HD1 G1/2-AG G3/8-IG

부품 번호...10.01.10.05809

Spring stroke Z: 50 mm

Shape mounting elements: Heavy Duty 1 spring plunger

Construction use: Mounting section



FST-STARR 50 HD2 G1/2-AG G3/8-IG

부품 번호...10.01.10.05805

Spring stroke Z: 50 mm

Shape mounting elements: Heavy Duty 2 spring plunger

Construction use: Mounting section

평 패드

FXP-SW70 442 3R18 O10O10 F

부품 번호...10.01.38.00690

<https://www.schmalz.com/10.01.38.00690>



FST-STARR 75 HD1 G1/2-AG G3/8-IG

부품 번호...10.01.10.05808

Spring stroke Z: 75 mm

Shape mounting elements: Heavy Duty 1 spring plunger

Construction use: Mounting section



FST-STARR 75 HD2 G1/2-AG G3/8-IG

부품 번호...10.01.10.05803

Spring stroke Z: 75 mm

Shape mounting elements: Heavy Duty 2 spring plunger

Construction use: Mounting section



MOD-FLAN 120x120 FXP-FMP

부품 번호...10.01.21.00244

Length L: 120 mm

Width B: 120 mm

Height H: 60 mm

Weight: 1.1 kg

Measuring range: bar

Construction use: Vacuum area gripping system FXP-FMP

평 패드

FXP-SW70 442 3R18 O10O10 F

부품 번호...10.01.38.00690

<https://www.schmalz.com/10.01.38.00690>



MOD-FLAN 176.6x118 FXP

부품 번호...10.01.38.01722

Length L: 176.6 mm

Width B: 118 mm

Height H: 40 mm

Construction use: Vacuum area gripping system FXP



VS-MONT 84x21x34.5 VSi-V FXP

부품 번호...10.01.38.02691

Length L: 84 mm

Width B: 21 mm

Height H: 34.5 mm

Construction use: Vacuum area gripping system FXP



SET fuer-Sensor(FXP/FMP)

부품 번호...10.01.38.01194

평 패드

FXP-SW70 442 3R18 O10O10 F

부품 번호...10.01.38.00690

<https://www.schmalz.com/10.01.38.00690>



SET FXC-FMC

부품 번호...10.01.21.01291

Length L: 119 mm

Width B: 119 mm

Height H: 9.6 mm

Measuring range: bar

Construction use: Vacuum area gripping system FXC-FMC



SET FXP-FMP

부품 번호...10.01.21.02407

Length L: 232 mm

Width B: 119 mm

Height H: 119 mm

Measuring range: bar

Construction use: Vacuum area gripping system FXP-FMP



SET FXP-FMP 4NUTSTEIN

부품 번호...10.01.21.00243

contains: 4 slot nuts

Measuring range: bar

Construction use: Vacuum area gripping system FXP-FMP

평 패드

FXP-SW70 442 3R18 O10O10 F

부품 번호...10.01.38.00690

<https://www.schmalz.com/10.01.38.00690>



VAM 40 V U BAR

부품 번호...10.07.02.00046

External diameter D: 40 mm

Measuring range: -1,00 ... 0,00 bar



VSL 12-9 PU MI-TR

부품 번호...10.07.09.00037

External diameter D: 12 mm

Internal diameter d: 9 mm

Length max.: 50 m

Material hose: PU

Bending radius min.: 70 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -20 ... 90 °C



NUT-STEI 20x20 M8-IG 10

부품 번호...25.09.06.00012

Width B: 20 mm

Height H: 4.9 mm

Material: Steel

Length L: 20 mm

Thread G1: M8-F

Shape mounting elements: With step

Surface: galvanised

Weight: 15.9 g

평 패드

FXP-SW70 442 3R18 O10O10 F

부품 번호...10.01.38.00690

<https://www.schmalz.com/10.01.38.00690>



NUT-STEI 20x20 M6-IG 10

부품 번호...25.09.06.00036

Width B: 20 mm

Height H: 5 mm

Material: Steel

Length L: 20 mm

Thread G1: M6-F

Shape mounting elements: With step

Surface: galvanised



ABDK-PROF-10x7x1450-KU-SW-FXP-FMP

부품 번호...26.07.03.00002

Length L: 1,450 mm

Width B: 10 mm

Height H: 7 mm

Material: Plastics

Measuring range: bar

Construction use: Vacuum area gripping system FXP-FMP



FLAN-PL 120x120x10 FXC-FMC

부품 번호...10.01.21.00313

Length L: 120 mm

Width B: 120 mm

Height H: 10 mm

Measuring range: bar

Construction use: Vacuum area gripping system FXC-FMC

평 패드

FXP-SW70 442 3R18 O10O10 F

부품 번호...10.01.38.00690

<https://www.schmalz.com/10.01.38.00690>



FLK G1/2-IG G1/2-AG V

부품 번호...10.01.03.00207

Thread G1: G1/2"-F

Thread G2: G1/2"-M

Operating temperature: 0 ... 70 °C

Shape mounting elements: Reinforced



VS-MONT 76.5x19 VSi FXP-FMP

부품 번호...10.01.38.02485

Length L: 76.5 mm

Width B: 19 mm

Add. function: Vacuum and pressure switch VSi

Measuring range: bar

Add. function: Vacuum and pressure switch

Construction use: Vacuum area gripping system FXP-FMP

예비 부품



ERS FXP-SEMP-50 DECKEL

부품 번호...10.01.38.02186

Measuring range: bar

Size: SEMP-50

contains: Cover

Construction use: Vacuum area gripping system FXP

평 패드

FXP-SW70 442 3R18 O10O10 F

부품 번호...10.01.38.00690

<https://www.schmalz.com/10.01.38.00690>



MASK-FOL SW70 402 3R18 FXP-FMP

부품 번호...10.01.38.00502

Length L: 402 mm

Width B: 109.8 mm

Height H: 0.4 mm

Arrangement suction cells: 3 rows, 18 mm

Measuring range: bar

Nozzle diameter: 0.7 mm

Construction use: Vacuum area gripping system FXP-FMP



SD 120x79x29 FXP

부품 번호...10.01.38.01607

Length L: 120 mm

Width B: 79 mm

Height H: 29 mm

Construction use: Vacuum area gripping system FXP



DI-PL 442-3R18 O10O10 F FXP-FMP

부품 번호...10.01.38.00192

Length L: 442 mm

Width B: 128 mm

Arrangement: 3R18

Material type: Foam O, Height 2x10 mm

Add. function: Filter

Construction use: Vacuum area gripping system FXP-FMP