

Bellows suction cup (round)

FG 62 NK-45 N018

부품 번호...10.01.06.00459

<https://www.schmalz.com/10.01.06.00459>

홈페이지 > 진공 자동화 기술 > 진공 부품 > 진공패드 > 주름 진공 패드 (원형) > FG 62 NK-45 N018

Bellows suction cup (round) for very uneven workpieces




Size: 62

Suction cup material: Natural Rubber NK

Material hardness [Shore A]: 45 Shore A

Number of folds: 2.5

디자인 데이터



속성

값

d	8 mm
d2	29.50 mm
D1	62 mm
Dk	18 mm
Dmax(S)	65 mm
Ds	62.20 mm
H	54 mm
H2	13 mm
Z (Stroke)	29 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

기술 데이터

속성	값
Suction force (-600mbar)	41.01 N
Pull-off force	137 N
Volume	61.122 cm ³
Curve radius (min) (convex)	75 mm
Size	62
Nipple family	N 018
Number of folds	2.50
Suction cup material	Natural Rubber NK

Schmalz에 문의

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8462403 |...에서 2
schmalz@schmalz.co.kr

Bellows suction cup (round)

FG 62 NK-45 N018

부품 번호...10.01.06.00459

<https://www.schmalz.com/10.01.06.00459>

Material hardness [Shore A]	45 Shore A
Weight	52 g
Product family	FG

부속품



SA-NIP N018 G1/4-AG DN440

부품 번호...10.01.06.01065

Nipple family: N 018

Thread G1: G1/4"-M

Length L1: 28.8 mm

Fitting length: 4 mm

Nominal diameter dn: 4.4 mm

Spanner size SW2: 5 mm

Material: Aluminum



SA-NIP N018 G1/4-IG DN440

부품 번호...10.01.06.01066

Nipple family: N 018

Thread G1: G1/4"-F

Length L1: 28.8 mm

Fitting length: 15 mm

Nominal diameter dn: 4.4 mm

Spanner size SW2: 5 mm

Material: Aluminum