

Bellows suction cup SI-MD (round)

FGA 16 SI-MD-55 N016

부품 번호...10.01.06.04115

<https://www.schmalz.com/10.01.06.04115>

홈페이지 > 진공 자동화 기술 > 진공 부품 > 진공패드 > 주름 진공 패드 (원형) > FGA 16 SI-MD-55 N016

Bellows suction cup (round) with optimal adaptation to uneven surfaces



Size: 16


Suction cup material: Silicone SI metal detectable

Material hardness [Shore A]: 55 Shore A

Material characteristics: FDA-compatible

Number of folds: 1.5

디자인 데이터



속성

값

d 4.50 mm

d2 8.40 mm

D1 17 mm

Dk 10 mm

Dmax(S) 18.50 mm

Ds 15.60 mm

H 19.20 mm

H2 3.80 mm

H3 9.40 mm

Z (Stroke) 6.70 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

기술 데이터

속성	값
Number of folds	1.50
Suction force (-600mbar)	2.30 N
Size	16
Suction cup material	Silicone SI metal detectable
Weight	1.30 g
Curve radius (min) (convex)	7 mm
Product family	FGA

Schmalz에 문의

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8462403 |...에서 3
schmalz@schmalz.co.kr

Bellows suction cup SI-MD (round)

FGA 16 SI-MD-55 N016

부품 번호...10.01.06.04115

<https://www.schmalz.com/10.01.06.04115>

부속품



SA-NIP N016 G1/8-AG DN310

부품 번호...10.01.06.04062

Nipple family: N 016

Thread G1: G1/8"-M

Length L1: 20 mm

Fitting length: 6 mm

Nominal diameter dn: 3.1 mm

Spanner size SW2: 3 mm

Material: Aust. Stainless steel



SA-NIP N016 M5-AG DN250

부품 번호...10.01.06.04365

Nipple family: N 016

Thread G1: M5-M

Length L1: 16 mm

Fitting length: 5 mm

Nominal diameter dn: 2.5 mm

Spanner size SW2: 3 mm

Material: Aust. Stainless steel



SA-NIP N016 M5-IG DN310

부품 번호...10.01.06.04689

Nipple family: N 016

Thread G1: M5-F

Length L1: 16 mm

Fitting length: 10 mm

Nominal diameter dn: 3.1 mm

Spanner size SW2: 3 mm

Material: Aust. Stainless steel

Bellows suction cup SI-MD (round)

FGA 16 SI-MD-55 N016

부품 번호...:10.01.06.04115

<https://www.schmalz.com/10.01.06.04115>



SA-NIP N016 G1/8-IG DN310

부품 번호...:10.01.06.04690

Nipple family: N 016

Thread G1: G1/8"-F

Length L1: 18.5 mm

Fitting length: 12 mm

Nominal diameter dn: 3.1 mm

Material: Aust. Stainless steel