

Bellows suction cups (round)

FSG 3 NBR-CO-55 M5-AG

부품 번호...10.01.06.03719

<https://www.schmalz.com/10.01.06.03719>

홈페이지 > 진공 자동화 기술 > 진공 부품 > 진공패드 > 주름 진공 패드 (원형) > Bellows Suction Cups FSG (2.5 Folds) > FSG 3 NBR-CO-55 M5-AG

Bellows suction cup (round) for very uneven workpieces



Size: 3

Suction cup material: Nitrile rubber NBR-conductive

Material hardness [Shore A]: 55 Shore A


Nipple material: Aluminum

Connection: M5-M

Number of folds: 2.5

Vacuum connection: M5-M

디자인 데이터



속성

값

d2 1.80 mm

dn 1 mm

Dmax(S) 4 mm

Ds 3 mm

G1 M5-M

H 10.20 mm

LG1 4.50 mm

SW1 7 mm

Z (Stroke) 1.10 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

기술 데이터

속성	값
Suction cup material	Nitrile rubber NBR-conductive
Material hardness [Shore A]	55 Shore A
Size	3
Number of folds	2.50
Connection	M5-AG
Curve radius (min) (convex)	4 mm
Volume	0.022 cm ³

Schmalz에 문의

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8402403 |...에서 2
schmalz@schmalz.co.kr

Bellows suction cups (round)

FSG 3 NBR-CO-55 M5-AG

부품 번호...10.01.06.03719

<https://www.schmalz.com/10.01.06.03719>

Suction force (-600mbar)	0.15 N
Pull-off force	0.40 N
Hose diameter (rec.) d	2 mm
Weight	0.70 g
Product family	FSG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Pull-off force: The pull-off force of the versions made of natural rubber is reduced by about 40% Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

예비 부품



SA-NIP N055 M5-AG DN100

부품 번호...10.01.01.13084

Thread G1: M5-M

Fitting length: 3.5 mm

Material: Aluminum



FG 3 NBR-CO-55 N055

부품 번호...10.01.06.03706

Size: 3

Suction cup material: Nitrile rubber NBR-conductive

Material hardness [Shore A]: 55 Shore A

Number of folds: 2.5