

Bellows suction cups (round)

FSGB 25 NBR-55 G1/8-AG

부품 번호...10.01.06.00112

<https://www.schmalz.com/10.01.06.00112>

홈페이지 > 진공 자동화 기술 > 진공 부품 > 진공패드 > 주름 진공 패드 (원형) > Bellows Suction Cups FSGB (3.5 Folds) > FSGB 25 NBR-55 G1/8-AG

Bellows suction cup (round) for very uneven workpieces



Size: 25


Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Nipple material: Aluminum

Number of folds: 3.5

디자인 데이터



속성

값

d2 10 mm

Dmax(S) 26.50 mm

dn 3.50 mm

Ds 23 mm

G1 G1/8"-M

H 51 mm

LG1 7.50 mm

SW1 14 mm

Z (Stroke) 22 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

기술 데이터

속성	값
Pull-off force	20 N
Size	25
Weight	9.80 g
Nipple family	N 049
Suction cup material	Nitrile rubber NBR
Suction force (-600mbar)	4.50 N
Hose diameter (rec.) d	4 mm

Schmalz에 문의

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8402403 | ...에서 2
schmalz@schmalz.co.kr

Bellows suction cups (round)

FSGB 25 NBR-55 G1/8-AG

부품 번호...10.01.06.00112

<https://www.schmalz.com/10.01.06.00112>

Volume	7.071 cm ³
Curve radius (min) (convex)	25 mm
Product family	FSGB
Number of folds	3.50

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

예비 부품



SA-NIP N049 G1/8-AG DN300

부품 번호...10.01.06.01693

Nipple family: N 049

Thread G1: G1/8"-M

Length L1: 21 mm

Fitting length: 4 mm

Nominal diameter dn: 3 mm

Material: Aluminum



FGB 25 NBR-55 N049

부품 번호...10.01.06.00109

Size: 25

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Number of folds: 3.5