

Flat suction cup (oval)

SGON 45x15 NBR-55 G1/4-IG

부품 번호...10.01.05.00097

<https://www.schmalz.com/10.01.05.00097>

홈페이지 > 진공 자동화 기술 > 진공 부품 > 진공패드 > 평면 진공 패드(타원형) > Flat Suction Cups SGON > SGON 45x15 NBR-55 G1/4-IG

Flat suction cup (oval) for long and also curved workpieces



Dimensions (LxB): 45 x 15


Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Nipple material: Aluminum

Connection: G1/4"-F

디자인 데이터



속성

값

Bmax(S) 16.50 mm

Bs 14.40 mm

dn 3 mm

G1 G1/4"-F

H 36 mm

LG1 12 mm

Lmax(S) 46 mm

Ls 44.40 mm

SW1 17 mm

Z (Stroke) 2 mm

Note: Acceptable dimensional tolerances for rubber parts concerning to DIN ISO 3302-1 M3.

기술 데이터

속성	값
Suction force (-600mbar)	28.20 N
Volume	2.306 cm ³
Curve radius (min) (convex)	10 mm
Hose diameter (rec.) d	6 mm
Dimensions (LxB)	45 x 15
Number of folds	0
Suction cup material	Nitrile rubber NBR

Schmalz에 문의

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8402403 |...에서 3
schmalz@schmalz.co.kr

Flat suction cup (oval)

SGON 45x15 NBR-55 G1/4-IG

부품 번호...10.01.05.00097

<https://www.schmalz.com/10.01.05.00097>

Material hardness [Shore A]

55 Shore A

Weight

14.30 g

Product family

SGON

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a smooth, dry workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

예비 부품



SA-NIP N023 G1/4-IG DN350

부품 번호...10.01.05.00121

Thread G1: G1/4"-F

Length L1: 25 mm

Fitting length: 15 mm

Nominal diameter dn: 3.5 mm

Material: Aluminum



ZOKL 15-18

부품 번호...10.07.10.00033

Clamping range: 15.0 ... 18.0 mm

Material: Galvanized steel

Flat suction cup (oval)

SGON 45x15 NBR-55 G1/4-IG

부품 번호...10.01.05.00097

<https://www.schmalz.com/10.01.05.00097>



SGO 45x15 NBR-55 N023

부품 번호...10.01.05.00153

Dimensions (LxB): 45 x 15

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A



ZOKL 15-18

부품 번호...10.07.10.00033

Clamping range: 15.0 ... 18.0 mm

Material: Galvanized steel