

Flat suction cup (oval)

SGON 30x10 NBR-55 G1/8-IG

부품 번호...10.01.05.00099

<https://www.schmalz.com/10.01.05.00099>

홈페이지 > 진공 자동화 기술 > 진공 부품 > 진공패드 > 평면 진공 패드(타원형) > Flat Suction Cups SGON > SGON 30x10 NBR-55 G1/8-IG

Flat suction cup (oval) for long and also curved workpieces



Dimensions (LxB): 30 x 10


Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Nipple material: Aluminum

Connection: G1/8"-F

디자인 데이터



속성

값

Bmax(S) 11.50 mm

Bs 9.40 mm

dn 2.50 mm

G1 G1/8"-F

H 25 mm

LG1 9 mm

Lmax(S) 30.50 mm

Ls 29.40 mm

SW1 14 mm

Z (Stroke) 1.50 mm

Note: Acceptable dimensional tolerances for rubber parts concerning to DIN ISO 3302-1 M3.

기술 데이터

속성	값
Suction force (-600mbar)	12.20 N
Volume	0.516 cm ³
Curve radius (min) (convex)	7.50 mm
Hose diameter (rec.) d	4 mm
Dimensions (LxB)	30 x 10
Number of folds	0
Suction cup material	Nitrile rubber NBR

Schmalz에 문의

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8462403 |...에서 3
schmalz@schmalz.co.kr

Flat suction cup (oval)

SGON 30x10 NBR-55 G1/8-IG

부품 번호...10.01.05.00099

<https://www.schmalz.com/10.01.05.00099>

Material hardness [Shore A]

55 Shore A

Weight

7.50 g

Product family

SGON

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a smooth, dry workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

예비 부품



SA-NIP N022 G1/8-IG DN350

부품 번호...10.01.05.00123

Thread G1: G1/8"-F

Length L1: 18.5 mm

Fitting length: 13 mm

Nominal diameter dn: 3.5 mm

Material: Aluminum



ZOKL 11-13

부품 번호...10.07.10.00032

Clamping range: 11.0 ... 13.0 mm

Material: Galvanized steel

Flat suction cup (oval)

SGON 30x10 NBR-55 G1/8-IG

부품 번호...10.01.05.00099

<https://www.schmalz.com/10.01.05.00099>



SGO 30x10 NBR-55 N022

부품 번호...10.01.05.00152

Dimensions (LxB): 30 x 10

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A



ZOKL 11-13

부품 번호...10.07.10.00032

Clamping range: 11.0 ... 13.0 mm

Material: Galvanized steel