

Flat suction cup (round)

PFYN 50 NBR-55 G1/8-IG

부품 번호...10.01.01.00091

<https://www.schmalz.com/10.01.01.00091>

홈페이지 > 진공 자동화 기술 > 진공 부품 > 진공패드 > 평면 진공 패드 (원형) > 평평한 흡입 컵 PFYN > PFYN 50 NBR-55 G1/8-IG

Flat suction cup (round) for smooth or slightly rough surfaces



Size: 50


Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Nipple material: Aluminum

Vacuum connection: G1/8"-F

디자인 데이터



속성

값

dn	3.50 mm
Dmax(S)	53.50 mm
Ds	50 mm
G1	G1/8"-F
H	31 mm
LG1	9 mm
SW1	14 mm
Z (Stroke)	4 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

기술 데이터

속성	값
Suction force (-600mbar)	91 N
Volume	7 cm ³
Curve radius (min) (convex)	75 mm
Hose diameter (rec.) d	4 mm
Size	50
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55 Shore A
Weight	17.30 g

Schmalz에 문의

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 84602403 | ...에서 3
schmalz@schmalz.co.kr

Flat suction cup (round)

PFYN 50 NBR-55 G1/8-IG

부품 번호...10.01.01.00091

<https://www.schmalz.com/10.01.01.00091>

Product family	PFYN
Number of folds	0

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

부속품



SU 50

부품 번호...10.01.01.12837

Size: 50

Clamping range: 45.0 ... 60.0 mm

Temperature resistance: 80 °C

예비 부품



SA-NIP N008 G1/8-IG DN350

부품 번호...10.01.01.03524

Thread G1: G1/8"-F

Length L1: 25 mm

Fitting length: 16 mm

Material: Aluminum

Spanner size SW2: 4 mm

Flat suction cup (round)

PFYN 50 NBR-55 G1/8-IG

부품 번호...10.01.01.00091

<https://www.schmalz.com/10.01.01.00091>



PFG 50 NBR-55 N008

부품 번호...10.01.01.00017

Size: 50

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A