

Flat suction cup (round)


PFYN 10 HT1-60 G1/8-IG

부품 번호...10.01.01.11148

<https://www.schmalz.com/10.01.01.11148>

홈페이지 > 진공 자동화 기술 > 진공 부품 > 진공패드 > 평면 진공 패드 (원형) > 평평한 흡입 컵 PFYN > PFYN 10 HT1-60 G1/8-IG

Flat suction cup (round) for smooth or slightly rough surfaces



Size: 10

Suction cup material: High temperature material HT1


Material hardness [Shore A]: 60 Shore A

Material property: non-marking

Nipple material: Aluminum

Vacuum connection: G1/8"-F

디자인 데이터



속성

값

dn	2 mm
Dmax(S)	11.50 mm
Ds	10 mm
G1	G1/8"-F
H	23.50 mm
LG1	9 mm
SW1	14 mm
Z (Stroke)	1.40 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

기술 데이터

속성	값
Suction force (-600mbar)	4 N
Volume	0.07 cm ³
Curve radius (min) (convex)	12.50 mm
Hose diameter (rec.) d	4 mm
Size	10
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60 Shore A
Weight	5.30 g

Schmalz에 문의

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8462403 |...에서 2
schmalz@schmalz.co.kr

Flat suction cup (round)

PFYN 10 HT1-60 G1/8-IG

부품 번호...10.01.01.11148

<https://www.schmalz.com/10.01.01.11148>

Product family	PFYN
Number of folds	0

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

예비 부품



SA-NIP N004 G1/8-IG DN200

부품 번호...10.01.01.03520

Thread G1: G1/8"-F

Length L1: 20 mm

Fitting length: 16 mm

Material: Aluminum



PFG 10 HT1-60 N004

부품 번호...10.01.01.11161

Size: 10

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A

Material property: non-marking