

Flat suction cup (round)

PFYN 2 HT1-60 M3-AG

부품 번호...10.01.01.13000

<https://www.schmalz.com/10.01.01.13000>

홈페이지 > 진공 자동화 기술 > 진공 부품 > 진공패드 > 평면 진공 패드 (원형) > 평평한 흡입 컵 PFYN > PFYN 2 HT1-60 M3-AG

Flat suction cup (round) for smooth or slightly rough surfaces



Size: 2

Suction cup material: High temperature material HT1


Material hardness [Shore A]: 60 Shore A

Material property: non-marking

Nipple material: Aluminum

Vacuum connection: M3-M

디자인 데이터



속성

값

dn	1 mm
Dmax(S)	2.50 mm
Ds	2 mm
G1	M3-M
H	6 mm
LG1	3 mm
SW1	5 mm
Z (Stroke)	0.50 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

기술 데이터

속성	값
Suction force (-600mbar)	0.12 N
Volume	0.001 cm ³
Curve radius (min) (convex)	2 mm
Hose diameter (rec.) d	2 mm
Size	2
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60 Shore A
Weight	1 g

Schmalz에 문의

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8402403 | ...에서 2
schmalz@schmalz.co.kr

Flat suction cup (round)

PFYN 2 HT1-60 M3-AG

부품 번호...10.01.01.13000

<https://www.schmalz.com/10.01.01.13000>

Product family	PFYN
Number of folds	0

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

예비 부품



SA-NIP N003 M3-AG DN100

부품 번호...10.01.01.00316

Thread G1: M3-M

Length L1: 7.5 mm

Fitting length: 2 mm

Material: Aluminum



PFG 2 HT1-60 N003

부품 번호...10.01.01.12967

Size: 2

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A