

Flat suction cup (round)

SHFN 50 NK-45 G1/4-AG MOS

부품 번호...10.01.01.11695

<https://www.schmalz.com/10.01.01.11695>

홈페이지 > 진공 자동화 기술 > 진공 부품 > 진공패드 > 평면 진공 패드 (원형) > 평평한 흡입 패드 SHFN > SHFN 50 NK-45 G1/4-AG MOS

Flat suction cup (round) for highly dynamic handling of wood



Size: 50

Suction cup material: Natural Rubber NK

Material hardness [Shore A]: 45 Shore A

Nipple material: Aluminum

Connection: G1/4-AG

디자인 데이터



속성

값

d2 21 mm

dn 4.40 mm

Dmax(S) 55 mm

Ds 52 mm

G1 G1/4"-M

H 26.20 mm

LG1 11 mm

SW1 17 mm

Z (Stroke) 3 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

기술 데이터

속성	값
Size	50
Suction cup material	Natural Rubber NK
Suction force d2	40 N
Suction force (-600mbar)	110 N
Lateral force	95 N
Volume	6.30 cm ³
Curve radius (min) (convex)	41 mm

Schmalz에 문의

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8402403 | ...에서 3
schmalz@schmalz.co.kr

Flat suction cup (round)

SHFN 50 NK-45 G1/4-AG MOS

부품 번호...10.01.01.11695

<https://www.schmalz.com/10.01.01.11695>

Hose diameter (rec.) d	4 mm
Number of folds	0
Weight	19.10 g
Product family	SHFN

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Pull-off force: The pull-off force of the versions made of natural rubber is reduced by about 40% Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

부속품



SIEB 15x0.8 MS-A2 0.103/0.07

부품 번호...10.07.01.00211

External diameter D: 15 mm

Length L: 0.8 mm

Material: Brass / Stainless steel

예비 부품



SA-NIP N041 G1/4-AG DN440

부품 번호...10.01.01.11772

Thread G1: G1/4"-M

Fitting length: 4 mm

Material: Aluminum

Flat suction cup (round)

SHFN 50 NK-45 G1/4-AG MOS

부품 번호...10.01.01.11695

<https://www.schmalz.com/10.01.01.11695>



SHF 50 NK-45 N041 MOS

부품 번호...10.01.01.11688

Size: 50

Suction cup material: Natural Rubber NK

Material hardness [Shore A]: 45 Shore A



DR 28/21x3 C03 EPDM-15 KE

부품 번호...10.01.06.01679

External diameter D: 28 mm

Internal diameter d: 21 mm

Height H: 3 mm

Material type: Foam C, Height 3 mm

Sealing material: EPDM

Material hardness [Shore A]: 15 Shore A

Add. function: Adhesive tape on one side