

Suction plate (round)

SPU 125 SI-60 G1/4-IG TV

부품 번호...10.01.01.01158

<https://www.schmalz.com/10.01.01.01158>

홈페이지 > 진공 자동화 기술 > 진공 부품 > 진공패드 > 평면 진공 패드 (원형) > Suction Plates SPU > SPU 125 SI-60 G1/4-IG TV

Suction plate (round), universal, for smooth and slightly rough surfaces




Size: 125

Suction cup material: Silicone SI

Material hardness [Shore A]: 60 Shore A

Connection: G1/4"-F

디자인 데이터



속성

값

d	22 mm
d2	83 mm
Dmax(S)	132 mm
Ds	125 mm
G1	G1/4"-F
G2	G1/4"-M
G3	G1/8"-F
H	25 mm
H1	43 mm
L2	22 mm
LG1	13 mm
LG2	13 mm
LG3	6 mm
Z (Stroke)	7 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

기술 데이터

속성	값
Suction force (-600mbar)	660 N
Suction force d2	365 N
Volume	75.40 cm ³

Schmalz에 문의

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8462403 | ...에서 3
schmalz@schmalz.co.kr

Suction plate (round)

SPU 125 SI-60 G1/4-IG TV

부품 번호...10.01.01.01158

<https://www.schmalz.com/10.01.01.01158>

Curve radius (min) (convex)	220 mm
Hose diameter (rec.) d	9 mm
Size	125
Suction cup material	Silicone SI
Material hardness [Shore A]	60 Shore A
Weight	240 g
Number of folds	0
Product family	SPU

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

부속품



SU 120

부품 번호...10.01.01.12437

Size: 120

Clamping range: 115.0 ... 130.0 mm

Temperature resistance: 80 °C

예비 부품



TV G1/4-AG 13

부품 번호...10.05.10.00061

Thread G1: G1/4"-M

Thread G2: G1/8"-F

Spring stroke Z: 13 mm

Schmalz에 문의

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8462402 |...에서 3
schmalz@schmalz.co.kr

Suction plate (round)

SPU 125 SI-60 G1/4-IG TV

부품 번호...10.01.01.01158

<https://www.schmalz.com/10.01.01.01158>



DR-SPU 125 SI-60

부품 번호...10.01.01.01100

Size: 125

Suction cup material: Silicone SI

Material hardness [Shore A]: 60 Shore A