

Flat suction cup (round)

SAF 60 NBR-45 M10-AG

부품 번호...10.01.01.11454

<https://www.schmalz.com/10.01.01.11454>

홈페이지 > 진공 자동화 기술 > 진공 부품 > 진공패드 > 시트메탈 핸들링용 진공 패드 > 평평한 흡입 컵 SAF > SAF 60 NBR-45 M10-AG

Flat suction cup (round) for very dynamic handling of smooth and oily workpieces



Size: 60


Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 45 Shore A

Nipple material: Steel

Connection: M10-AG

디자인 데이터



속성

값

dn	4 mm
Dmax(S)	67 mm
Ds	60.60 mm
G1	M10-M
H	31 mm
LG1	12 mm
SW1	22 mm
Z (Stroke)	6 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

기술 데이터

속성	값
Suction force (-600mbar)	150 N
Lateral force	105 N
Lateral force (oily surface)	85 N
Volume	16.70 cm ³
Curve radius (min) (convex)	75 mm
Hose diameter (rec.) d	6 mm
Size	60

Schmalz에 문의

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8462403 |...에서 2
schmalz@schmalz.co.kr

Flat suction cup (round)

SAF 60 NBR-45 M10-AG

부품 번호...10.01.01.11454

<https://www.schmalz.com/10.01.01.11454>

Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	45 Shore A
Weight	60.70 g
Number of folds	0
Product family	SAF

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Lateral force: The specified lateral forces are values measured at a vacuum of -0.6 bar with a dry or oily, smooth, flat workpiece surface. Depending on the workpiece surface and its quality, the actual values may deviate from these values Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

부속품



SU 60

부품 번호...10.01.01.13585

Size: 60

Clamping range: 60.0 ... 70.0 mm

Temperature resistance: 80 °C