

Flat suction cup (oval)

SAOF 80x40 HT2-65 G3/8-IG

부품 번호...10.01.05.00749

<https://www.schmalz.com/10.01.05.00749>

홈페이지 > 진공 자동화 기술 > 진공 부품 > 진공패드 > 시트메탈 핸들링용 진공 패드 > Flat Suction Cups SAOF HT2 (Oval) > SAOF 80x40 HT2-65 G3/8-IG

Flat suction cup (oval) for very dynamic handling



Dimensions (LxB): 80 x 40


Suction cup material: High temperature material HT2

Material hardness [Shore A]: 65 Shore A

Nipple material: Nickel plated

Connection: G3/8-IG

디자인 데이터



속성

값

Bmax(S) 43 mm

Bs 38.60 mm

dn 6 mm

G1 G3/8"-F

H 28 mm

LG1 9 mm

Lmax(S) 85 mm

Ls 80.60 mm

SW1 22 mm

Z (Stroke) 4 mm

기술 데이터

속성	값
Suction force (-600mbar)	140 N
Lateral force	108 N
Volume	10.70 cm ³
Curve radius (min) (convex)	50 mm
Hose diameter (rec.) d	4 mm
Dimensions (LxB)	80 x 40
Connection	G3/8"-F
Number of folds	0

Schmalz에 문의

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 84602403 |...에서 2
schmalz@schmalz.co.kr



Flat suction cup (oval)

SAOF 80x40 HT2-65 G3/8-IG

부품 번호...:10.01.05.00749

<https://www.schmalz.com/10.01.05.00749>

Suction cup material	High temperature material HT2
Material hardness [Shore A]	65 Shore A
Temperature resistance	200 °C
Weight	64.10 g
Product family	SAOF

Schmalz에 문의

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8462402 |...에서 2
schmalz@schmalz.co.kr