

Bellows suction cup (round)

SPB2 20 SI-40 SW130 P

부품 번호...10.01.06.03222

<https://www.schmalz.com/10.01.06.03222>

홈페이지 > 벨로우즈 흡입 컵 SPB2 P (2.5 배) 흐름 저항 > SPB2 20 SI-40 SW130 P

Bellows suction cup (round) with 2.5 corr. for dynamic handling of cardboard and rigid packaging




Size: 20

Suction cup material: Silicone SI

Material hardness [Shore A]: 40 Shore A

Height H: 24.3 mm

디자인 데이터



속성

값

d	8.50 mm
d1	11.80 mm
d2	10.20 mm
d5	7.90 mm
dn	1.30 mm
D1	20 mm
Dmax(S)	20.50 mm
Ds	19.60 mm
H	24.30 mm
H2	2.20 mm
H3	8.20 mm
H5	2 mm
Z (Stroke)	9 mm

기술 데이터

속성	값
Suction force (-600mbar)	4.90 N
Pull-off force	8 N
Volume	2.50 cm ³
Curve radius (min) (convex)	25 mm
Size	20

Schmalz에 문의

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8462403 |...에서 3
schmalz@schmalz.co.kr

Bellows suction cup (round)

SPB2 20 SI-40 SW130 P

부품 번호...10.01.06.03222

<https://www.schmalz.com/10.01.06.03222>

Number of folds	2.50
Suction cup material	Silicone SI
Material hardness [Shore A]	40 Shore A
Weight	2.50 g
Product family	SPB2

부속품



FD 16 120

부품 번호...10.01.06.02565

External diameter D: 16 mm

Filter pore size: 120 µm

Construction use: Bellows suction cup

Size: FG20/FGA20

예비 부품



SW 130 P 7.3

부품 번호...10.05.04.00092

Shape: Push In

Length L: 15.5 mm

Material: Polyoxymethylene

External diameter D: 7.3 mm

Bellows suction cup (round)

SPB2 20 SI-40 SW130 P

부품 번호...10.01.06.03222

<https://www.schmalz.com/10.01.06.03222>



SPB2 20 SI-40 P

부품 번호...10.01.06.03125

Size: 20

Suction cup material: Silicone SI

Material hardness [Shore A]: 40 Shore A

Number of folds: 2.5

Shape: Push In