

Schorsing, opgelapt

FST-C 100-HD1

Onderdeelnr...:10.01.20.01260

<https://www.schmalz.com/10.01.20.01260>

Homepage > Suspension Clampable FST-C > FST-C 100-HD1

Opschorting met hoogtecompensatie en pneumatische fixatie Heavy-Duty



Shape mounting elements: Heavy Duty 1 spring plunger

Spring stroke Z: 100 mm


Weight: 9 kg

Length L: 170 mm

Width B: 170 mm

Height H: 50 mm

Ontwerpgegevens



Attribuut	Waarde
B	170 mm
B1	410 mm
B2	45 mm
H	50 mm
H1	89,40 mm
L	170 mm
L1	250 mm
L2	220 mm
Z (Stroke)	100 mm

Accessoires

Contact opnemen met Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Schorsing, opgelapt

FST-C 100-HD1

OnderdeelNr...:10.01.20.01260

<https://www.schmalz.com/10.01.20.01260>



EMV 5 24V-DC 3/2 NO

OnderdeelNr...:10.05.01.00068

Nominal size: 5 mm

Voltage DC: 24V - DC

Function: 3/2-way valve

Control valve: Normally open

Connecting thread: G1/4"-IG

Pressure range (operating pressure): bar

Power consumption DC: 8 W



MOD-FLAN 157x120 SBX-C

OnderdeelNr...:10.01.20.01274

Weight: 1,77 kg

Length L: 157 mm

Width B: 120 mm

Height H: 60 mm

Construction use: Large-area vacuum gripper-C



MOD-FLAN 157x120 SBX-C

OnderdeelNr...:10.01.20.01275

Weight: 1,77 kg

Length L: 157 mm

Width B: 120 mm

Height H: 60 mm

Construction use: Large-area vacuum gripper-C

Schorsing, opgelapt

FST-C 100-HD1

Onderdeelnr...:10.01.20.01260

<https://www.schmalz.com/10.01.20.01260>



PROP-VENT 24V-DC DC

Onderdeelnr...:10.05.05.00104

Thread G1: G1/8"-F

Voltage: 24V - DC

Current type: Direct current



STV-GE G1/4-AG 6

Onderdeelnr...:10.08.02.00205

Thread G1: G1/4"-M

Hose diameter: 6 mm

Material: Brass

Operating temperature: -20 ... 80 °C

External diameter D: 11,2 mm

Length L: 15,2 mm