

Veerstoter

FSTE-HDB G1/4-AG 25 VG-AB

Onderdeelnr...:10.01.02.01427

<https://www.schmalz.com/10.01.02.01427>

Homepage > Vacuümtechniek voor de automatisering > Vacuüm componenten > Bevestigingsmiddelen > Veerstoters > Spring Plungers FSTE-HDB > FSTE-HDB G1/4-AG 25 VG-AB

Veerstoter met demping en hoogtecompensatie, Heavy-Duty




Suction cup connection: G1/4"-AG

Vacuum connection: G1/8"-IG

Spring stroke Z: 25 mm

Shape mounting elements: with anti-rotation guard anti-block

Ontwerpgegevens



Attribuut	Waarde
G1	G1/8"-F
G2	G1/4"-AG
G3	M20x1.5-AG
H	118,30 mm
H2	34,80 mm
LG1	12 mm
LG2	8,50 mm
LG3	44 mm
SW1	24 mm
SW2	17 mm
SW3	22 mm
Z (Stroke)	25 mm

Aanbeveling: Vermijd de maximale slag van de ram Z bij continu gebruik om de levensduur te verlengen

Technische gegevens

Attribuut	Waarde
Shape mounting elements	with anti-rotation guard anti-block
Spring rate	0,71 N/mm
Spring pretension	3,06 N
Spring force, center	11,95 N
Vertical load	2400 N

Contact opnemen met Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Horizontal load	747 N
Weight	235 g
Operating temperature	0 ... 80 °C
Product family	FSTE-HDB

Note: Spring force: Referred to 50 % of operating stroke Vertical load: Maximum static loading Horizontal load: The specification of the horizontal load refers to the lower edge of the plunger with extended spring. It is a maximum static stress and it impairs the spring compression and extension in horizontal position.

Accessoires



FLK G1/4-IG G1/4-AG

Part no...:10.01.03.00178

Thread G1: G1/4"-F

Thread G2: G1/4"-AG

Operating temperature: 0 ... 70 °C



KGL G1/4-IG G1/4-AG

Part no...:10.01.03.00110

Thread G1: G1/4"-F

Thread G2: G1/4"-AG

Height H: 37,5 mm

Veerstoter

FSTE-HDB G1/4-AG 25 VG-AB

Onderdeelnr...:10.01.02.01427

<https://www.schmalz.com/10.01.02.01427>



KGL G1/4-IG M10x1.25-AG

Part no...:10.01.03.00137

Thread G1: G1/4"-F

Thread G2: M10x1.25-AG

Height H: 37,5 mm



FLK G1/4-IG M10x1.25-AG

Part no...:10.01.03.00206

Thread G1: G1/4"-F

Thread G2: M10x1.25-AG

Operating temperature: 0 ... 70 °C



HTR-STA 55 1N D20 WI

Part no...:10.08.03.00086

Length L: 55 mm

Connection 1: 1 Nutenstein

Connection of suction cup, spring plunger: Afmeting D20-G1/4

Shape: Haaks

Veerstoter

FSTE-HDB G1/4-AG 25 VG-AB

Onderdeelnr...:10.01.02.01427

<https://www.schmalz.com/10.01.02.01427>



HTR-UNI 2N FSTE-HDB

Part no...:10.01.03.00332

Operating temperature: °C

Shape: voor FSTE-HDB

Cross-beam connection: 2 T-slots



ST G1/8-AG 4 MS-ROH

Part no...:10.08.03.00153

Thread G1: G1/8"-M

Hose diameter (rec.) d: 4 mm

Material: Brass

Surface: rauw

Length L: 4 mm

Nominal diameter dn: 2,5 mm



ST G1/8-AG 6 MS-V

Part no...:10.08.03.00154

Thread G1: G1/8"-M

Hose diameter (rec.) d: 6 mm

Material: Brass

Surface: vernikkeld

Length L: 5 mm

Nominal diameter dn: 4,4 mm

Veerstoter

FSTE-HDB G1/4-AG 25 VG-AB

Onderdeelnr...:10.01.02.01427

<https://www.schmalz.com/10.01.02.01427>



ST G1/8-AG 9 MS-V

Part no...:10.08.03.00155

Thread G1: G1/8"-M

Hose diameter (rec.) d: 9 mm

Material: Brass

Surface: vernikkeld

Length L: 5 mm

Nominal diameter dn: 4 mm



STV-GE G1/8-AG 4

Part no...:10.08.02.00202

Thread G1: G1/8"-M

Hose diameter: 4 mm

Material: Brass

Operating temperature: -20 ... 80 °C

External diameter D: 7,9 mm

Length L: 13,7 mm



STV-GE G1/8-AG 6

Part no...:10.08.02.00204

Thread G1: G1/8"-M

Hose diameter: 6 mm

Material: Brass

Operating temperature: -20 ... 80 °C

External diameter D: 11,4 mm

Length L: 16,4 mm

Contact opnemen met Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Veerstoter

FSTE-HDB G1/4-AG 25 VG-AB

Onderdeelnr...:10.01.02.01427

<https://www.schmalz.com/10.01.02.01427>



STV-GE G1/8-AG 8

Part no...:10.08.02.00206

Thread G1: G1/8"-M

Hose diameter: 8 mm

Material: Brass

Operating temperature: °C

External diameter D: 14 mm

Length L: 20,7 mm



STV-W G1/8-AG 4

Part no...:10.08.02.00156

Thread G1: G1/8"-M

Hose diameter: 4 mm

Material: Nickel plated

Operating temperature: -20 ... 80 °C

Length L: 16,4 mm



STV-W G1/8-AG 6

Part no...:10.08.02.00158

Thread G1: G1/8"-M

Hose diameter: 6 mm

Material: Nickel plated

Operating temperature: -20 ... 80 °C

Length L: 20,1 mm

Veerstoter

FSTE-HDB G1/4-AG 25 VG-AB

Onderdeelnr...:10.01.02.01427

<https://www.schmalz.com/10.01.02.01427>



STV-W G1/8-AG 8

Part no...:10.08.02.00160

Thread G1: G1/8"-M

Hose diameter: 8 mm

Material: Nickel plated

Operating temperature: -20 ... 80 °C

Length L: 24 mm



STV-GE G1/8-AG 6 HT

Part no...:10.08.02.00389

Thread G1: G1/8"-M

Hose diameter: 6 mm

Material: Brass

Operating temperature: -20 ... 120 °C

External diameter D: 11,6 mm

Length L: 19 mm



STV-W G1/8-AG 6

Part no...:10.08.02.00288

Thread G1: G1/8"-M

Hose diameter: 6 mm

Material: Plastics

Operating temperature: °C

Length L: 20,8 mm

Contact opnemen met Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Veerstoter

FSTE-HDB G1/4-AG 25 VG-AB

Onderdeelnr...:10.01.02.01427

<https://www.schmalz.com/10.01.02.01427>



STV-W G1/8-AG 6 HT

Part no...:10.08.02.00391

Thread G1: G1/8"-M

Hose diameter: 6 mm

Material: Brass

Operating temperature: -20 ... 120 °C

Length L: 22,5 mm



STV-WF G1/8-AG 4

Part no...:10.08.02.00166

Thread G1: G1/8"-M

Hose diameter: 4 mm

Material: Nickel plated

Operating temperature: -10 ... 70 °C

Length L: 17,4 mm



STV-WF G1/8-AG 6

Part no...:10.08.02.00168

Thread G1: G1/8"-M

Hose diameter: 6 mm

Material: Nickel plated

Operating temperature: -10 ... 70 °C

Length L: 21,4 mm

Veerstoter

FSTE-HDB G1/4-AG 25 VG-AB

Onderdeelnr.:10.01.02.01427

<https://www.schmalz.com/10.01.02.01427>



STV-WF G1/8-AG 8

Part no.:10.08.02.00170

Thread G1: G1/8"-M

Hose diameter: 8 mm

Material: Nickel plated

Operating temperature: -10 ... 70 °C

Length L: 23,4 mm



STV-WF G1/8-AG 10

Part no.:10.08.02.00257

Thread G1: G1/8"-M

Hose diameter: 10 mm

Material: Nickel plated

Operating temperature: -10 ... 70 °C

Length L: 25,2 mm



STV-T G1/8-AG 4

Part no.:10.09.02.00039

Thread G1: G1/8"-M

Hose diameter: 4 mm

Material: Brass

Operating temperature: °C

Length L: 32,5 mm

Veerstoter

FSTE-HDB G1/4-AG 25 VG-AB

Onderdeelnr...:10.01.02.01427

<https://www.schmalz.com/10.01.02.01427>



STV-T G1/8-AG 6

Part no...:10.09.02.00040

Thread G1: G1/8"-M

Hose diameter: 6 mm

Material: Brass

Operating temperature: °C

Length L: 41,5 mm



STV-T G1/8-AG 8

Part no...:10.09.02.00041

Thread G1: G1/8"-M

Hose diameter: 8 mm

Material: Brass

Operating temperature: °C

Length L: 48,7 mm