

Veerstoter

FSTI G3/8-AG G1/8-AG 10

Onderdeelnr...:10.01.02.00755

<https://www.schmalz.com/10.01.02.00755>

Homepage > Vacuümtechniek voor de automatisering > Vacuüm componenten > Bevestigingsmiddelen > Veerstoters > Spring Plungers FSTI > FSTI G3/8-AG G1/8-AG 10

Veerstoter met inwendige demperven en hoogtecompensatie




Suction cup connection: G3/8"-AG

Vacuum connection: G1/8"-AG

Spring stroke Z: 10 mm

Ontwerpgegevens



Attribuut	Waarde
G1	G1/8"-M
G2	G3/8"-AG
G3	M18x1.5-AG
H	72 mm
H2	22 mm
LG1	6,50 mm
LG2	9 mm
LG3	41 mm
SW1	27 mm
SW2	13 mm
SW3	19 mm
Z (Stroke)	10 mm

Technische gegevens

Attribuut	Waarde
Spring rate	0,10 N/mm
Spring pretension	7,08 N
Spring force, center	7,57 N
Vertical load	1000 N
Horizontal load	700 N
Weight	150 g

Contact opnemen met Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Operating temperature

0 ... 80 °C

Note: Spring force: Referred to 50 % of operating stroke Vertical loading: Maximum static loading Horizontal stress: The specification of the horizontal stress refers to the lower edge of the plunger with extended spring. It is a maximum static stress and it impairs the spring compression and extension in horizontal position

Accessoires



HTR-FST A2 FSTI

Onderdeelnr...:10.01.03.06134

Cross-beam connection: Bolt adapter A2

Thread G1: M18x1.5-IG

Construction use: Spring plunger



HTR-FST A3 FSTI

Onderdeelnr...:10.01.03.06136

Cross-beam connection: Ball head 28.5 mm

Thread G1: M18x1.5-IG

Construction use: Spring plunger

Veerstoter

FSTI G3/8-AG G1/8-AG 10

Onderdeelnr...:10.01.02.00755

<https://www.schmalz.com/10.01.02.00755>



HTR-FST 2N

Onderdeelnr...:10.01.03.06143

Cross-beam connection: 2 T-slots

Thread G1: M18x1.5-IG



HTR-UNI 2N FSTI

Onderdeelnr...:10.01.03.00297

Operating temperature: °C

Shape: voor FSTI

Cross-beam connection: 2 T-slots



RED-STK G1/2-AG G3/8-IG MS-V

Onderdeelnr...:10.08.04.00096

Thread G1: G1/2"-M

Thread G2: G3/8"-IG

Material: Brass

Surface: vernikkeld

Length L: 6 mm

Veerstoter

FSTI G3/8-AG G1/8-AG 10

OnderdeelNr...:10.01.02.00755

<https://www.schmalz.com/10.01.02.00755>



STVI-GE G1/8-IG 4

OnderdeelNr...:10.08.02.00149

Thread G1: G1/8"-F

Hose diameter: 4 mm

Material: Brass

Operating temperature: -20 ... 80 °C

External diameter D: 8,5 mm

Length L: 23,5 mm



STVI-GE G1/8-IG 6

OnderdeelNr...:10.08.02.00150

Thread G1: G1/8"-F

Hose diameter: 6 mm

Material: Brass

Operating temperature: -20 ... 80 °C

External diameter D: 11,5 mm

Length L: 26,5 mm



STVI-GE G1/8-IG 8

OnderdeelNr...:10.08.02.00151

Thread G1: G1/8"-F

Hose diameter: 8 mm

Material: Brass

Operating temperature: -20 ... 80 °C

External diameter D: 14,5 mm

Length L: 29,5 mm