

Transportejector

SEC-60

Onderdeelnr.: 10.02.01.01079

<https://www.schmalz.com/10.02.01.01079>

Homepage > Feed Ejectors SEC > SEC-60

Transportejector voor bijzonder poreuze onderdelen




Nozzle size: 6 mm

Suction rate (max.): 12,9 m³/h

Material: Aluminum

Ontwerpgegevens



Attribuut	Waarde
D	32 mm
D1	12,50 mm
D2	12,50 mm
G2	M5-IG
G3	M3-IG
L	14 mm
L1	44 mm
LG3	5 mm
X1	25 mm

Technische gegevens

Attribuut	Waarde
Max. vacuum	-245 mbar
Suction rate (max.)	215 l/min
Suction rate (max.)	12,90 m³/h
Air consumption suction	140 l/min
Air consumption suction	6,60 m³/h
Pressure range (operating pressure)	2,0 ... 5,0 bar
Operating temperature	°C
Material	Aluminum
Weight	0,04 kg

Contact opnemen met Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Transportejector

SEC-60

Onderdeelnr...:10.02.01.01079

<https://www.schmalz.com/10.02.01.01079>

Max. vacuum	-7,23 inHg
Suction rate (max.)	7,59 cfm
Air consumption suction	4,94 cfm
Pressure range (operating pressure)	29,0 ... 72,5
Product family	SEC

Note: Air consumption: At optimal operating pressure (4,5 bar)