

## Zweefzuiger

SBS 20 HF M5-IG AL

Onderdeelnr...:10.01.01.12650

<https://www.schmalz.com/10.01.01.12650>

Homepage > Vacuümtechniek voor de automatisering > Vacuüm componenten > Speciale grijpers > Zwevende zuignappen > Zwevende zuignappen  
SBS > SBS 20 HF M5-IG AL

### Zweefzuiger voor de handling van zeer gevoelige werkstukken




Diameter: 20 mm

Shape: High Flow

Compressed-air connection: M5-IG

Material: Aluminum

### Ontwerpgegevens



| Attribuut | Waarde   |
|-----------|----------|
| B         | 22,20 mm |
| D         | 20 mm    |
| G1        | M5-F     |
| G2        | M3-IG    |
| G3        | M5-IG    |
| H         | 17 mm    |
| H1        | 17,50 mm |
| LG1       | 5 mm     |
| LG2       | 6 mm     |
| LG3       | 6 mm     |
| X1        | 15 mm    |

### Technische gegevens

| Attribuut                           | Waarde          |
|-------------------------------------|-----------------|
| Holding force                       | 3 N             |
| Air consumption                     | 8,40 m³/h       |
| Air consumption                     | 140 l/min       |
| Pressure range (operating pressure) | 1,0 ... 6,0 bar |
| Weight                              | 12 g            |
| Product family                      | SBS             |

### Contact opnemen met Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | [info@schmalz.nl](mailto:info@schmalz.nl)

## Zweefzuiger

SBS 20 HF M5-IG AL

Onderdeelnr...:10.01.01.12650

<https://www.schmalz.com/10.01.01.12650>

Note: Air consumption: The values provided are based on an operating pressure of 5 bar, measured on a suction-tight workpiece. The actual values may differ depending on the properties of the workpiece.

### Onderdelen



#### REIB-FL SBS HT1-60

Onderdeelnr...:10.01.01.12585

Construction use: Floating suction cup

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A

External diameter D: 2,5 mm