

Basisejector


SBP-C 15 G02 NO A

Onderdeelnr...:10.02.01.00626
<https://www.schmalz.com/10.02.01.00626>




Homepage > Vacuümtechniek voor de automatisering > Vacuüm componenten > Vacuümgenerator > Basic ejectoren > Basic Ejectors SBP-C with Additional Functions > SBP-C 15 G02 NO A

Basisejector "BASE-PUMP-controlled" in bijzondere lichte bouwvorm



Nozzle diameter: 1,5 mm
Degree of evacuation: 85 %
Connection: G1/8"(1)-G1/8"(2)
Pressure optimal: 5 bar
Suction rate (max.): 71 l/min
Air consumption suction: 118 l/min
Control valve: Normally open
construction shape compact ejectors: Blow-off function

Ontwerpgegevens



Attribuut	Waarde
B	15 mm
d	4,20 mm
D	13,50 mm
G1	G1/8"-F
G2	G1/8"-IG
G3	G1/8"-IG
H	51 mm
H1	50 mm
H2	5,20 mm
H3	8,50 mm
L	106 mm
L1	146 mm
L2	19 mm
L3	29,50 mm
SW1	14 mm
SW2	14 mm
X1	20 mm

Technische gegevens

Attribuut	Waarde
-----------	--------

Basisejector

SBP-C 15 G02 NO A

Onderdeelnr...:10.02.01.00626

<https://www.schmalz.com/10.02.01.00626>

Nozzle diameter	1,50 mm
Degree of evacuation	85 %
Suction rate (max.)	4,30 m³/h
Suction rate (max.)	71 l/min
Air consumption suction	7,10 m³/h
Air consumption suction	118 l/min
Sound level free	72 dB(A)
Sound level suction	65 dB(A)
Pressure range (operating pressure)	3,0 ... 6,0 bar
Pressure optimal	5 bar
Recomm. internal hose diameter compressed air	4 mm
Recomm. internal hose diameter vacuum	6 mm
Weight	70 g
Operating temperature	0 ... 50 °C
Pressure range (operating pressure)	43,5 ... 87,0
Pressure optimal	72,50 psi
Suction rate (max.)	2,51 cfm
Air consumption suction	4,17 cfm
Air consumption blow off	1,06 cfm
Product family	SBP-C

Note: The supply voltage for vacuum switches and solenoid valves is 24 VDC Air consumption: On version with solenoid valves SBP-C 07 (24) / SBP-C 25 (320) and optimal operating pressure Hose diameter: For max. length 2 m

Accessoires



BEF-PL 110x44.5x3 SBP

Onderdeelnr...:10.02.01.00511

Length L: 110 mm

Width B: 44,5 mm

Height H: 3 mm

Construction use: Basic ejector SBP

Contact opnemen met Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Basisejector

SBP-C 15 G02 NO A

Onderdeelnr...:10.02.01.00626

<https://www.schmalz.com/10.02.01.00626>



SET SBP M4-IG

Onderdeelnr...:10.02.01.00769

Length L: 50 mm

Width B: 14 mm

Construction use: Basic ejector SBP

Type: M4-IG



ASK B-MIC10 3000 K-2P

Onderdeelnr...:21.04.06.00086

Material hose: PUR cable

Electrical connection: Stekker 10mm



VFT G1/4-IG 80

Onderdeelnr...:10.07.01.00119

Connection: G1/4"-IG

Shape: Short filter insert

Nominal flow rate: 110 l/min

Nominal flow rate: 6,6 m³/h

Filter pore size: 80 µm

Onderdelen

Contact opnemen met Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Basisejector

SBP-C 15 G02 NO A

Onderdeelnr...:10.02.01.00626

<https://www.schmalz.com/10.02.01.00626>



SD G1/8-AG 14x40

Onderdeelnr...:10.02.01.00540

Thread G1: G1/8"-M

External diameter D: 14 mm

Length L: 40 mm