

Basisejector

SBP HV 3 16 22 KU

Onderdeelnr...:10.02.01.01962

<https://www.schmalz.com/10.02.01.01962>

Homepage > Vacuümtechniek voor de automatisering > Vacuüm componenten > Vacuümgenerator > Basic ejectoren > Basic Ejectors SBP-HV/HF
With Plastic Main Body > SBP HV 3 16 22 KU

Basisejector voor universeel gebruik



Shape: High Vacuum

Number of stages: 3

Nozzle diameter: 1,6 mm

Size: 22


Degree of evacuation: 90 %

Suction rate (max.): 308,8 l/min

Air consumption suction: 103 l/min

Material: Plastics

Ontwerpgegevens



Attribuut	Waarde
B	31,50 mm
d2	6,20 mm
D	20 mm
G1	G1/4"-F
G2	G3/8"-IG
G5	M6-IG
H	45 mm
H2	6,50 mm
H3	22,50 mm
L	80 mm
L1	171 mm
L2	24,50 mm
L3	26,50 mm
L4	153 mm
SW2	14 mm
X1	22 mm
X2	26 mm
Y1	22 mm

Technische gegevens

Contact opnemen met Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Basisejector

SBP HV 3 16 22 KU

Onderdeelnr...:10.02.01.01962

<https://www.schmalz.com/10.02.01.01962>

Attribuut	Waarde
Nozzle diameter	1,60 mm
Number of stages	3
Degree of evacuation	90 %
Suction rate (max.)	308,80 l/min
Air consumption suction	6,34 m³/h
Air consumption suction	103 l/min
Sound level free	80 dB(A)
Sound level suction	72 dB(A)
Pressure range (operating pressure)	2,0 - 6,0 bar
Recomm. internal hose diameter compressed air	6 mm
Recomm. internal hose diameter vacuum	12 mm
Weight	208,40 g
Operating temperature	0 ... 60 °C
Pressure range (operating pressure)	28,8 - 86,8
Suction rate (max.)	10,90 cfm
Air consumption suction	3,64 cfm
Product family	SBP-HV-HF-KU

Accessoires



SD 29x70 SHC 22

Onderdeelnr...:10.02.01.01517

External diameter D: 29 mm

Length L: 70 mm

Construction use: Schmalz Holder Cap

Size: 22

Basisejector

SBP HV 3 16 22 KU

Onderdeelnr...:10.02.01.01962

<https://www.schmalz.com/10.02.01.01962>



SD 29x121.5 SHC

Onderdeelnr...:10.02.01.01831

External diameter D: 29 mm

Length L: 121,5 mm

Construction use: Schmalz Holder Cap

Onderdelen



SFE 22 POM

Onderdeelnr...:10.02.01.01767

Hole diameter: 22 mm

Width B: 31,5 mm

Height H: 45 mm

Length L: 80 mm

Thread G1: G1/4"-F

Thread G2: G3/8"-IG

Compressed-air connection: G1/4"-IG

Suction cup connection: G3/8"-IG



SEP HV 3 16 22

Onderdeelnr...:10.02.01.01397

Shape: High Vacuum

Number of stages: 3

Nozzle size: 1,6 mm

Hole diameter: 22 mm

Degree of evacuation: 90 %

Pressure range (operating pressure): 2,0 ... 6,0 bar

Pressure optimal: 4 bar

Suction rate (max.): 308,8 l/min

Air consumption suction: 103 l/min

Contact opnemen met Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Basisejector

SBP HV 3 16 22 KU

Onderdeelnr...:10.02.01.01962

<https://www.schmalz.com/10.02.01.01962>



SHC 3 22

Onderdeelnr...:10.02.01.01514

Number of stages: 3

Hole diameter: 22 mm

External diameter D: 20 mm

Length L: 73 mm

Thread G1: M27x1.5-M