

Schmalz X-Pump

SXPi 30 NO Q 2xM12-5

Onderdeelnr...:10.02.02.03783

<https://www.schmalz.com/10.02.02.03783>

Homepage > Vacuümtechniek voor de automatisering > Vacuüm componenten > Vacuümgenerator > Compacte ejectoren > Compacte uitwerpers
X-Pump SXPi / SXMPi met IO-Link > SXPi 30 NO Q 2xM12-5

Compacte ejector met Condition Monitoring, digit. Luchtspaarfunctie



Nozzle diameter: 3 mm

Control valve: Normally open

Electrical connection: 2xStekker M12, 5+5 pol

Communication: IO-Link (Class A)

Suction rate (max.): 220 l/min

Air consumption suction: 380 l/min


Pressure range (operating pressure): 3,0 ... 6,0 bar

Max. vacuum: 850 mbar

Sound level free: 72 dB(A)

Protection type IP: IP 65

Ontwerpgegevens



Attribuut	Waarde
B	39 mm
d	5,50 mm
G2	M12x1-AG
H	108 mm
H1	120 mm
H2	54 mm
H3	6 mm
L	210 mm
L2	5 mm
L3	97 mm
X1	89 mm
Y1	10 mm

Technische gegevens

Attribuut	Waarde
Nozzle diameter	3 mm
Degree of evacuation	85 %
Suction rate (max.)	220 l/min
Suction rate (max.)	13,20 m³/h
Suction rate (max.)	7,77 cfm
Air consumption suction	380 l/min

Contact opnemen met Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Schmalz X-Pump

SXPi 30 NO Q 2xM12-5

Onderdeelnr...:10.02.02.03783

<https://www.schmalz.com/10.02.02.03783>

Air consumption suction	22,80 m³/h
Air consumption suction	13,42 cfm
Sound level free	72 dB(A)
Pressure range (operating pressure)	43,5 ... 87,0
Pressure range (operating pressure)	3,0 ... 6,0 bar
Max. air consumption blow off	200 l/min
Air consumption blow off	7,06 cfm
Air consumption blow off	12 m³/h
Recomm. internal hose diameter compressed air	8 mm
Recomm. internal hose diameter vacuum	9 mm
Control valve	Normally open
Weight	0,82 kg
Operating temperature	0 ... 50 °C
Product family	SXPi

Note: The supply voltage for vacuum switches and solenoid valves is 24V DC Air consumption: At optimal operating pressure Hose diameter: For max. length 2 m

Accessoires



ASK B-M12-5 5000 K-5P

Onderdeelnr...:21.04.05.00080

Electrical connection: Bus M12, 5 pol

Cable length: 5.000 mm

Material hose: PUR cable

Contact opnemen met Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Schmalz X-Pump

SXPi 30 NO Q 2xM12-5

Onderdeelnr...:10.02.02.03783

<https://www.schmalz.com/10.02.02.03783>



GPQ1 122x46x43 SXPi/SXMPi

Onderdeelnr...:10.02.02.02473

Length L: 122 mm

Width B: 46 mm

Height H: 43 mm

Number of connections: 1

Construction use: Compact ejectors SXPi/SXMPi



GPQ2 122x87x48 SXPi/SXMPi

Onderdeelnr...:10.02.02.02154

Length L: 122 mm

Width B: 87 mm

Height H: 48 mm

Number of connections: 2

Construction use: Compact ejectors SXPi/SXMPi

Onderdelen



SD 96x54x40 SXPi/SXMPi

Onderdeelnr...:10.02.02.02124

Length L: 96 mm

Width B: 54 mm

Height H: 40 mm

Construction use: Compact ejectors SXPi/SXMPi

Contact opnemen met Schmalz


Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Schmalz X-Pump

SXPi 30 NO Q 2xM12-5

Onderdeelnr...:10.02.02.03783

<https://www.schmalz.com/10.02.02.03783>



VST SXPi-25-30-SD

Onderdeelnr...:10.02.02.04283

Construction use: Schmalz X-Pump SXPi

Size: 25-30-SD

contains: Sieve/silencer/RSV