

Ejector module

SEP HV 2 07 13 S

Onderdeelnr...:10.02.01.01406

<https://www.schmalz.com/10.02.01.01406>

Homepage > Vacuümtechniek voor de automatisering > Vacuüm componenten > Vacuümgenerator > Ejectormodules > Uitwerpmodules ecoPump
SEP > SEP HV 2 07 13 S

Vacuümset meertrapsejector



Shape: High Vacuum

Number of stages: 2

Nozzle size: 0,7 mm

Hole diameter: 13 mm

construction shape compact ejectors: With safety valve

Degree of evacuation: 85 %


Pressure range (operating pressure): 2,0 ... 6,0 bar

Pressure optimal: 4 bar

Suction rate (max.): 37,5 l/min

Air consumption suction: 23,5 l/min

Ontwerpgegevens



Attribuut	Waarde
D1	5,40 mm
D2	12,80 mm
L1	5 mm
L2	41,50 mm
L3	55,50 mm

Technische gegevens

Attribuut	Waarde
Weight	3,60 g
Operating temperature	0 ... 60 °C
Recomm. internal hose diameter compressed air	4 mm
Recomm. internal hose diameter vacuum	6 mm
Pressure range (operating pressure)	2,0 ... 6,0 bar
Pressure range (operating pressure)	29,0 ... 87,0
Pressure optimal	4 bar
Pressure optimal	58 psi

Contact opnemen met Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Ejector module

SEP HV 2 07 13 S

Onderdeelnr...:10.02.01.01406

<https://www.schmalz.com/10.02.01.01406>

Sound level free	72 dB(A)
Sound level suction	62 dB(A)
construction shape compact ejectors	S
Suction rate (max.)	2,30 m³/h
Suction rate (max.)	37,50 l/min
Suction rate (max.)	1,32 cfm
Air consumption suction	1,45 m³/h
Air consumption suction	23,50 l/min
Air consumption suction	0,83 cfm
Degree of evacuation	85 %
Number of stages	2
Nozzle size	0,70 mm
Hole diameter	13 mm
Shape	High Vacuum
Product family	SEP

Accessoires



SHC 2 13

Onderdeelnr...:10.02.01.01496

Number of stages: 2

Hole diameter: 13 mm

External diameter D: 14,2 mm

Length L: 18 mm

Thread G1: M16x1-M

Ejector module

SEP HV 2 07 13 S

Onderdeelnr...:10.02.01.01406

<https://www.schmalz.com/10.02.01.01406>



SD 16.5x51.5 SHC 13

Onderdeelnr...:10.02.01.01498

External diameter D: 16,5 mm

Length L: 51,5 mm

Construction use: Schmalz Holder Cap

Size: 13



SFE 13 AL

Onderdeelnr...:10.02.01.01419

Hole diameter: 13 mm

Width B: 23 mm

Height H: 33 mm

Length L: 51,5 mm

Thread G1: G1/8"-F

Thread G2: G1/4"-IG

Compressed-air connection: G1/8"-IG

Suction cup connection: G1/4"-IG

Vacuum connection: G1/8"-IG



SFE 13 POM

Onderdeelnr...:10.02.01.01807

Hole diameter: 13 mm

Width B: 23 mm

Height H: 33 mm

Length L: 46,5 mm

Thread G1: G1/8"-F

Thread G2: G1/4"-IG

Compressed-air connection: G1/8"-IG

Suction cup connection: G1/4"-IG

Ejector module

SEP HV 2 07 13 S

OnderdeelNr...:10.02.01.01406

<https://www.schmalz.com/10.02.01.01406>



BEF-WIN 36x40x27 5 SFE-13

OnderdeelNr...:10.08.03.00314

Width B: 36 mm

Height H: 40 mm

Length L: 27 mm

Construction use: Schmalz Fixation Element

Size: 13



SET SFE 13

OnderdeelNr...:10.02.01.01579

Width B: 20 mm

Height H: 20 mm

Length L: 27 mm

Construction use: Schmalz Fixation Element

Size: 13

Thread G1: G1/8"-M

Thread G2: M8-AG



SEV G1/8-IG G1/8-AG

OnderdeelNr...:10.02.01.01519

External diameter D: 19 mm

Length L: 39,5 mm

Thread G1: G1/8"-F

Thread G2: G1/8"-AG

Onderdelen

Contact opnemen met Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Ejector module

SEP HV 2 07 13 S

Onderdeelnr...:10.02.01.01406

<https://www.schmalz.com/10.02.01.01406>



ERS SEP-13 6xRUE-KLAP

Onderdeelnr...:10.02.01.01449

Construction use: Ejector module

Size: 13

contains: 6x flap