

Vacuümventilator

SB 90 330 1.5 IE3-TYP3

Onderdeelnr...:10.04.01.00088

<https://www.schmalz.com/10.04.01.00088>

Homepage > Vacuümtechniek voor de automatisering > Vacuüm componenten > Vacuümgenerator > Vacuümventilator > Vacuum Blowers SB > SB 90 330 1.5 IE3-TYP3

Vacuümventilator



Suction rate (50 Hz): 90 m³/h

Suction rate (60 Hz): 110 m³/h

Vacuum (50 Hz): 330 mbar

Vacuum (60 Hz): 350 mbar

Rated power 50 Hz: 1,5 kW

Rated power 60 Hz: 1,8 kW

Voltage at 50Hz: D200V/Y350V ±10 %


Voltage at 60Hz: D220V/Y380-400V ±10%

Construction: IE3:JPN/KOR/BRA

Permission: IE3

Weight: 28,5 kg

Ontwerpgegevens



Attribuut	Waarde
B	306 mm
B1	317 mm
d	10,20 mm
D2	60 mm
G1	G1-1/2"-F
H	357 mm
L	431 mm
X1	240 mm
Y1	240 mm

Technische gegevens

Attribuut	Waarde
Suction rate (50 Hz)	90 m³/h
Suction rate (50 Hz)	1.499,90 l/min
Suction rate (60 Hz)	110 m³/h
Vacuum (50 Hz)	330 mbar
Vacuum (60 Hz)	350 mbar
Protection type IP	IP 55

Contact opnemen met Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Vacuümventilator

SB 90 330 1.5 IE3-TYP3

Onderdeelnr...:10.04.01.00088

<https://www.schmalz.com/10.04.01.00088>

Rated power 50 Hz	1,50 kW
Rated power 60 Hz	1,80 kW
Voltage at 50Hz	D200V/Y350V ±10 %
Voltage at 60Hz	
Sound level at 50 Hz	63,70 dB(A)
Noise level (60 Hz)	68,40 dB(A)
Weight	28,50 kg
Construction	IE3-TYP3
Construction	IE3:JPN/KOR/BRA
Product family	SB

Noise level according to DIN EN ISO 3744 (uncertainty factor KpA = 3 dB(A)), interval of 1 m, at medium load, both connection sides piped

Accessoires



SBB-230V-AC-ST/ABS-LUE SB

Onderdeelnr...:10.04.04.00234

Construction use: Blower SB

Voltage DC: 230V - AC

Material: Steel/ABS

Thread G1: G2"-M

Length L: 661 mm

Width B: 586 mm

Height H: 563 mm



SBB-24V-DC-ST/ABS-LUE SB

Onderdeelnr...:10.04.04.00319

Construction use: Blower SB

Voltage DC: 24V - DC

Material: Steel/ABS

Thread G1: G2"-M

Length L: 661 mm

Width B: 586 mm

Height H: 563 mm

Contact opnemen met Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Vacuümventilator

SB 90 330 1.5 IE3-TYP3

Onderdeelnr...:10.04.01.00088

<https://www.schmalz.com/10.04.01.00088>



STF 60 P 4.5 SSD

Onderdeelnr...:10.07.01.00259

Connection: Ø60mm

Shape: Piclon housing

Nominal flow rate: 270 m³/h

Filter pore size: 3 µm

Additional function: Hose clamps SSD