

Vacuümcup (ovaal)

SPLO 100x30 NBR-55

Onderdeelnr...:10.01.05.00182

<https://www.schmalz.com/10.01.05.00182>

Homepage > Vacuümtechniek voor de automatisering > Vacuüm componenten > Vacuümzuignappen > Vlakke zuignappen (ovaal) > Suction Plates
SPLO > SPLO 100x30 NBR-55

Vlakke vacuümgrijper (ovaal) voor lange of gewelfde werkstukken




Dimensions (LxB): 100 x 30

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Height H: 21 mm

Ontwerpgegevens



Attribuut	Waarde
Bk	30 mm
Bmax(S)	33,50 mm
Bs	28,70 mm
H	21 mm
H2	6 mm
Lk	120 mm
Lmax(S)	102,80 mm
Ls	98 mm
Z (Stroke)	5 mm

Opmerking: Toelaatbare maattoleranties voor elastomeeronderdelen volgens DIN ISO 3302-1 M3

Technische gegevens

Attribuut	Waarde
Suction force (-600mbar)	126 N
Volume	10,02 cm ³
Curve radius (min) (convex)	25 mm
Number of folds	0
Dimensions (LxB)	100 x 30
Suction cup material	Nitrile rubber NBR
Weight	200 g

Contact opnemen met Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Vacuümcup (ovaal)

SPLO 100x30 NBR-55

Onderdeelnr.:10.01.05.00182

<https://www.schmalz.com/10.01.05.00182>

Product family

SPLO

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor
