

Bellows suction cups (round)

SPB2 40 ED-65 G1/4-AG

Część nr.: 10.01.06.03459

<https://www.schmalz.com/10.01.06.03459>

Strona główna > Technologia podciśnienia w automatyce > Komponenty podciśnieniowe > Chwytyki powierzchniowe i efekторы końcowe > Podciśnieniowe urządzenia końcowe VEE > Przyssawki do efektorów końcowych podciśnienia > SPB2 40 ED-65 G1/4-AG

Bellows suction cup (round) for very uneven workpieces



Size: 40


Suction cup material: Elastodur ED

Material hardness [Shore A]: 65 Shore A

Thread G1: G1/4"-M

Number of folds: 2,5

Dane projektowe



Atrybut

Wartość

d2	22,90 mm
dn	6,10 mm
D1	42,20 mm
Dmax(S)	44,50 mm
Ds	41,30 mm
G1	G1/4"-M
H	52,20 mm
LG1	10 mm
SW1	17 mm
SW2	6 mm
Z (Stroke)	25 mm

Dane techniczne

Atrybut

Wartość

Suction force (-600mbar)	24,80 N
Pull-off force	40,50 N
Lateral force	20,30 N
Volume	27,90 cm ³
Curve radius (min) (convex)	60 mm
Hose diameter (rec.) d	6 mm

Kontakt z firmą Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl

Bellows suction cups (round)

SPB2 40 ED-65 G1/4-AG

Część nr.:10.01.06.03459

<https://www.schmalz.com/10.01.06.03459>

Size	40
Number of folds	2,50
Suction cup material	Elastodur ED
Material hardness [Shore A]	65 Shore A
Weight	23,10 g
Product family	SPB2

Note: Suction force: The specified suction forces are theoretical values with a dry, smooth and flat workpiece surface - they do not include safety factors

Akcesoria



SPI 40 PA SPB2-40

Część nr.:10.01.06.04044

Size: 40

Material: Polyamide

Use: SPB2-40



SC 050 G1/8-AG MOD

Część nr.:10.01.06.02849

Connection geometry: 050

Connection: G1/8"-M

Length L1: 24 mm

Fitting length: 7,2 mm

Nominal diameter dn: 4,4 mm

Bellows suction cups (round)

SPB2 40 ED-65 G1/4-AG

Część nr.:10.01.06.03459

<https://www.schmalz.com/10.01.06.03459>



SC-SW 60 6

Część nr.:10.05.04.00096

Spanner size SW1: 6 mm

Nominal size: 60



SC-SW 80 6

Część nr.:10.05.04.00097

Spanner size SW1: 6 mm

Nominal size: 80



SC-SW 100 6

Część nr.:10.05.04.00098

Spanner size SW1: 6 mm

Nominal size: 100

Bellows suction cups (round)

SPB2 40 ED-65 G1/4-AG

Część nr.:10.01.06.03459

<https://www.schmalz.com/10.01.06.03459>



SC-SW 120 6

Część nr.:10.05.04.00099

Spanner size SW1: 6 mm

Nominal size: 120



SC-SW 200 6

Część nr.:10.05.04.00100

Spanner size SW1: 6 mm

Nominal size: 200



SC-SW 240 6

Część nr.:10.05.04.00101

Spanner size SW1: 6 mm

Nominal size: 240

Części zamienne

Kontakt z firmą Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl

Bellows suction cups (round)

SPB2 40 ED-65 G1/4-AG

Część nr.:10.01.06.03459

<https://www.schmalz.com/10.01.06.03459>



SC 050 G1/4-AG MOD

Część nr.:10.01.06.02487

Connection geometry: 050

Connection: G1/4"-M

Length L1: 26,5 mm

Fitting length: 7,2 mm

Nominal diameter dn: 6,1 mm



SPB2 40 ED-65 SC050

Część nr.:10.01.06.03412

Size: 40

Suction cup material: Elastodur ED

Material hardness [Shore A]: 65 Shore A

Height H: 45 mm