

Schmalz X-Pump

SXMPi 25 NC H M12-8

Część nr...10.02.02.03808

<https://www.schmalz.com/10.02.02.03808>

Strona główna > Technologia podciśnienia w automatyce > Komponenty podciśnieniowe > Generatory podciśnienia > Ejektory kompaktowe > Wyrzutniki kompaktowe X-Pump SXPi / SXMPi z IO-Link > SXMPi 25 NC H M12-8

Compact ejector ""X-Pump-M"" with Condition Monitoring and power blow-off function



Nozzle diameter: 2,5 mm

Control valve: Normally closed

Electrical connection: Male connect M12, 8 pol

Communication: IO-Link (Class A)

Suction rate (max.): 185 l/min

Air consumption suction: 290 l/min


Pressure range (operating pressure): 3.0 ... 6.0 bar

Max. vacuum: -850 mbar

Sound level free: 67 dB(A)

Protection type IP: IP 65

Dane projektowe



Atrybut	Wartość
B	39 mm
B2	6,80 mm
d	5,50 mm
G1	G3/8"-F
G2	M12x1-M
G3	M5-F
H	108 mm
H1	160 mm
H2	54 mm
H3	6 mm
H4	26 mm
L	210 mm
L2	5 mm
L3	97 mm
L4	35,50 mm
X1	89 mm
X2	42 mm
Y1	10 mm
Y2	24 mm

Kontakt z firmą Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl

Schmalz X-Pump

SXMPi 25 NC H M12-8

Część nr.:10.02.02.03808

<https://www.schmalz.com/10.02.02.03808>



Dane techniczne

Atrybut	Wartość
Nozzle diameter	2,50 mm
Degree of evacuation	85 %
Suction rate (max.)	185 l/min
Suction rate (max.)	11,10 m³/h
Suction rate (max.)	6,53 cfm
Air consumption suction	290 l/min
Air consumption suction	17,40 m³/h
Air consumption suction	10,24 cfm
Sound level free	67 dB(A)
Pressure range (operating pressure)	43.5 ... 87.0
Pressure range (operating pressure)	3.0 ... 6.0 bar
Max. air consumption blow off	320 l/min
Recomm. internal hose diameter compressed air	8 mm
Recomm. internal hose diameter vacuum	9 mm
Control valve	Normally closed
Weight	0,91 kg
Operating temperature	0 ... 50 °C
Product family	SXMPi

Note: The supply voltage for vacuum switches and solenoid valves is 24V DC Air consumption: At optimal operating pressure Hose diameter: For max. length 2 m

Akcesoria



ASK B-M12-8 5000 K-8P

Część nr.:21.04.05.00079

Electrical connection: Fem connect M12, 8 pol

Cable length: 5 000 mm

Material hose: PUR cable

Kontakt z firmą Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl

Schmalz X-Pump

SXMPi 25 NC H M12-8

Część nr.:10.02.02.03808

<https://www.schmalz.com/10.02.02.03808>

Części zamienne



SD 96x54x40 SXPi/SXMPI

Część nr.:10.02.02.02124

Length L: 96 mm

Width B: 54 mm

Height H: 40 mm

Construction use: Compact ejectors SXPi/SXMPI



VST SXMPi-25-30-SD

Część nr.:10.02.02.04543

Construction use: Schmalz X-Pump SXMPi

Size: 25-30-SD

contains: Sieve/silencer/RSV