

Schmalz X-Pump

SXMPi 30 IMP Q 2xM12-5

Część nr...:10.02.02.03823

<https://www.schmalz.com/10.02.02.03823>

Strona główna > Technologia podciśnienia w automatyce > Komponenty podciśnieniowe > Generatory podciśnienia > Ejektory kompaktowe > Wyrzutniki kompaktowe X-Pump SXPi / SXMPi z IO-Link > SXMPi 30 IMP Q 2xM12-5

Compact ejector ""X-Pump-M"" with Condition Monitoring and power blow-off function



Nozzle diameter: 3 mm

Control valve: Double pilot valve

Electrical connection: 2xConnect M12, 5+5 pol

Communication: IO-Link (Class A)

Suction rate (max.): 220 l/min

Air consumption suction: 380 l/min


Pressure range (operating pressure): 3.0 ... 6.0 bar

Max. vacuum: -850 mbar

Sound level free: 72 dB(A)

Protection type IP: IP 65

Dane projektowe



Atrybut	Wartość
B	39 mm
d	5,50 mm
G2	M12x1-M
H	108 mm
H1	146 mm
H2	54 mm
H3	6 mm
H4	26 mm
L	210 mm
L2	5 mm
L3	97 mm
X1	89 mm
Y1	10 mm

Dane techniczne

Atrybut	Wartość
Nozzle diameter	3 mm
Degree of evacuation	85 %
Suction rate (max.)	220 l/min
Suction rate (max.)	13,20 m³/h

Kontakt z firmą Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl

Schmalz X-Pump

SXMPi 30 IMP Q 2xM12-5

Część nr.:10.02.02.03823

<https://www.schmalz.com/10.02.02.03823>

Suction rate (max.)	7,77 cfm
Air consumption suction	380 l/min
Air consumption suction	22,80 m³/h
Air consumption suction	13,42 cfm
Sound level free	72 dB(A)
Pressure range (operating pressure)	43.5 ... 87.0
Pressure range (operating pressure)	3.0 ... 6.0 bar
Max. air consumption blow off	320 l/min
Recomm. internal hose diameter compressed air	8 mm
Recomm. internal hose diameter vacuum	9 mm
Control valve	Double pilot valve
Weight	0,96 kg
Operating temperature	0 ... 50 °C
Product family	SXMPi

Note: The supply voltage for vacuum switches and solenoid valves is 24V DC Air consumption: At optimal operating pressure Hose diameter: For max. length 2 m

Akcesoria



ASK B-M12-5 5000 K-5P

Część nr.:21.04.05.00080

Electrical connection: Fem connect M12, 5 pol

Cable length: 5 000 mm

Material hose: PUR cable

Kontakt z firmą Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl

Schmalz X-Pump

SXMPi 30 IMP Q 2xM12-5

Część nr.:10.02.02.03823

<https://www.schmalz.com/10.02.02.03823>



GPQ1 122x46x43 SXPi/SXMPi

Część nr.:10.02.02.02473

Length L: 122 mm

Width B: 46 mm

Height H: 43 mm

Number of connections: 1

Construction use: Compact ejectors SXPi/SXMPi



GPQ2 122x87x48 SXPi/SXMPi

Część nr.:10.02.02.02154

Length L: 122 mm

Width B: 87 mm

Height H: 48 mm

Number of connections: 2

Construction use: Compact ejectors SXPi/SXMPi

Części zamienne



SD 96x54x40 SXPi/SXMPi

Część nr.:10.02.02.02124

Length L: 96 mm

Width B: 54 mm

Height H: 40 mm

Construction use: Compact ejectors SXPi/SXMPi

Kontakt z firmą Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl

Schmalz X-Pump

SXMPi 30 IMP Q 2xM12-5

Część nr.:10.02.02.03823

<https://www.schmalz.com/10.02.02.03823>



VST SXMPi-25-30-SD

Część nr.:10.02.02.04543

Construction use: Schmalz X-Pump SXMPi

Size: 25-30-SD

contains: Sieve/silencer/RSV